

596-00613

Article Number: 596-00613

Solar Label, Caution - Solar Electric System Connected Reflective Label, 6.5" X 1.0", Yellow, 50/pkg

**CAUTION: SOLAR ELECTRIC
SYSTEM CONNECTED**



Base Data

Local Order Number	596-00613
Type	CSESC
Color	Yellow (YE)
Features and Benefits	<ul style="list-style-type: none"> • Made with UV stable inks and materials for durability and weather resistance. • The labels are supplied with aggressive adhesive to ensure long life. • Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
Color of Print	Black (BK)
Product Description	HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Technical Description	6.5" X 1" Black text on a yellow background that reads as: "CAUTION - SOLAR ELECTRIC SYSTEM CONNECTED" in 3/8" tall characters using reflective inks. 50 per pkg.
Short Description	Solar Label, Caution - Solar Electric System Connected Reflective Label, 6.5" X 1.0", Yellow, 50/pkg

Product Dimensions

Width W (imperial)	6.5 "
Width W (metric)	165.1 mm
Height H (imperial)	1.0 "
Height H (metric)	25.4 mm

Logistics and Packaging

Quantity per	pack
Package Quantity (imperial)	50
Package Quantity	50

Material and Specifications

Material	Vinyl
Material Shortcut	Vinyl
Adhesive	Acrylic
Shortcut Adhesive	Acryl
Adhesive Operating Temperature	-40 °F to +302 °F (-40 °C to +150 °C)
Halogenfree	Yes
Operating Temperature	-40 °F to +180 °F (-40 °C to +82 °C)

ROHS Conformity Yes

UL Recognized (US) Yes