

Connector - C-SCFI 1,5/2,8X0,8 - 3240049

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Slip-on sleeve, red, 0.5 - 1.5 mm², 2.8 x 0.8

Why buy this product

- Electrolytic tin plating
- Hard-soldered crimping zone for maximum pull-out forces
- Halogen-free
- 'EASY ENTRY' for easy and reliable conductor entry
-



Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 452670
Weight per Piece (excluding packing)	0.64 g
Custom tariff number	85369010
Country of origin	China

Technical data

Dimensions

Length (b)	18.5 mm
Width (a)	2.8 mm
Length of insulation sleeve (c)	10.5 mm
Inner dimension of the insulating collar (d)	4.1 mm
Material thickness (g)	0.25 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
---------------------------------	-------------------

General

Color	red
-------	-----

Connector - C-SCFI 1,5/2,8X0,8 - 3240049

Technical data

General

Stripping length	7 mm
Components	Halogen-free
Material	Brass

Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details

Connector - C-SCFI 1,5/2,8X0,8 - 3240049

Approvals

EAC

EAC

Drawings

Dimensional drawing

