

## Female test connector - PSB 3/10/4 - 0601292

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Female test connector, Color: silver

The illustration shows various versions of the article

### Product Features

- Test sockets PSB ... are used for a reliable test connection
- With PSB 6/5/6, the test plug with a 4 mm diameter is used
- All test sockets are screwed into the bridge shaft
- With PSB 3/10/4 and PSB 4/7/6, the test connection is provided by the miniature test plug MPS with a 2.3 mm diameter



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 003012
Weight per Piece (excluding packing)	0.94 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### Dimensions

Length	10 mm
Width	4 mm
Pin diameter	2.40 mm

#### General

Color	silver
-------	--------

# Female test connector - PSB 3/10/4 - 0601292

## Technical data

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27440313

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

Approvals

EAC / EAC

---

Ex Approvals

---

Approvals submitted

---

## Female test connector - PSB 3/10/4 - 0601292

### Approvals

#### Approval details

EAC

EAC

### Drawings

Dimensional drawing

