

CAD50U7

contactor - TeSys K, D, S - CAD-50 - 5 NO -
instantaneous - 10 A - 240 V AC



Main

Range of product	TeSys D
Product or component type	Auxiliary contactor
Device short name	CAD
Contactor application	Control circuit
Utilisation category	AC-14 AC-15
Control circuit type	AC
Suppressor technology	Without built-in
Pole contact composition	5 NO
[Uc] control circuit voltage	240 V AC 50/60 Hz
Connections - terminals	Screwclamp terminal 1 cable 1...4 mm ² - cable stiffness: flexible - with cable end Screwclamp terminal 1 cable 1...4 mm ² - cable stiffness: flexible - without cable end Screwclamp terminal 1 cable 1...4 mm ² - cable stiffness: solid - without cable end Screwclamp terminal 2 cable 1...2.5 mm ² - cable stiffness: flexible - with cable end Screwclamp terminal 2 cable 1...4 mm ² - cable stiffness: flexible - without cable end Screwclamp terminal 2 cable 1...4 mm ² - cable stiffness: solid - without cable end

Complementary

Contact operation	Mechanically linked conforming to IEC 60947-5-1
Control circuit voltage limits	0.3...0.6 U _c drop-out 0.8...1.1 U _c operational 50 Hz 0.85...1.1 U _c operational 60 Hz
[Ui] rated insulation voltage	600 V - certifications CSA 600 V - certifications UL 690 V - overvoltage category III (pollution degree 3) - conforming to IEC 60947-5-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Tightening torque	1.7 N.m - on screwclamp terminal
[U _e] rated operational voltage	<= 690 V AC 25...400 Hz
[I _{th}] conventional free air thermal current	10 A at <= 60 °C
I _{rms} rated making capacity	140 A at <= 690 V AC conforming to IEC 60947-5-1
Associated fuse rating	10 A gG at <= 690 V conforming to IEC 60947-5-1
Inrush power in VA	70 VA at 20 °C
Hold-in power consumption in VA	8 VA at 20 °C 50 Hz
Mechanical durability	30000000 cycles
Operating rate	3 cyc/s at 20 °C
Operating time	12...22 ms coil energisation and NO closing 4...12 ms coil de-energisation and NO opening 4...19 ms coil energisation and NC opening 6...16 ms coil de-energisation and NC closing
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 ms on de-energisation between NC and NO contacts 1.5 ms on energisation between NC and NO contacts
Insulation resistance	> 10 MOhm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Height	77 mm
Width	45 mm
Depth	86 mm
Product weight	0.58 kg

Environment

Standards	BS 4794 EN 60947-5 IEC 60947-5-1 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-40...70 °C at U _c -5...60 °C at 0.8...1.1 U _c
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating in temperature
Shock resistance	10 gn control relay open 15 gn control relay closed
Vibration resistance	2 gn 5...300 Hz control relay open 4 gn 5...300 Hz control relay closed