






Technical drawing of a rectangular plate with the following specifications:

- Overall Dimensions:**
 - Width: 72,64
 - Height: 2,54
- Internal Features:**
 - Holes:** A grid of 24 holes, arranged in 2 rows and 12 columns.
 - Label: "All holes 1)"
 - Symbol: $\varnothing 0,05$
 - Distance from Left Edge:** 0,74
 - Distance Between Hole Centers:** 2,54
 - Distance Between Hole Columns:** $2,54 \times 24 = (60,96)$
 - 1st Contact:** Indicated on the right side of the hole grid.
 - Min. $\varnothing 2,8$:** Minimum diameter specification for the contact area.

09 18 550 7921	3	4,5
09 18 550 6921	2	4,5
09 18 550 5921	0,76 $\mu\text{m Au}$	4,5
09 18 550 7923	3	2,9
09 18 550 6923	2	2,9
09 18 550 5923	0,76 $\mu\text{m Au}$	2,9
Part number	Performance level	a

				Det.	Name		SEK 18 Male Connector Standard 50 poles Angled pins Without locking levers	Maßstab/ Scale 1,5:1
34890	01/02/08	PK	Detail.	01/12/99	JB			
29753	11/03/02	JB	Insp.					
29739	03/12/01	JB	Stand.					
27931	15/06/00	JB	HARTING EURL F-95972 Paris				TB 09 18 550 X92X	Blatt/ Page 2 / 2
26554	01/12/99	JB						
Mod.	Det.	Name					Sub.	