





GERMAN TYPE SNAP RING PLIERS EXTERNAL CLOSE STRAIGHT **New**

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72031	5"	125	8-25	6	36	5.0
72032	7"	175	19-60	6	36	8.0
72033	9"	225	35-100	6	36	12.0
72034	13"	325	85-165	6	36	22.0

- Made of alloy steel with heating treatment
- Black finish surface prevents rusty





GERMAN TYPE SNAP RING PLIERS EXTERNAL CLOSE CURVED **New**

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72041	5"	125	8-25	6	36	5.0
72042	7"	175	19-60	6	36	8.0
72043	9"	225	35-100	6	36	12.0
72044	13"	325	85-165	6	36	22.0

- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



ENERGY SAVING TYPE - LINESMAN

PART NO.	SIZE INCH	L MM			G.W. (kg)
72201	6"	150	6	48	16.4
72202	7"	175	6	48	19.6
72203	8"	200	6	36	19.0

- High leverage.
- Double cutting power.

ANSI B107.20M  
DIN 5244



ENERGY SAVING TYPE - DIAGONAL CUTTING



PART NO.	SIZE INCH	L MM			G.W. (kg)
72301	6"	150	6	48	11.9

- High leverage.
- Double cutting power.

ANSI B107.11M  
DIN 5238



ENERGY SAVING TYPE - DIAGONAL CUTTING

PART NO.	SIZE INCH	L MM			G.W. (kg)
72302	7"	175	6	36	12.6

- High leverage.
- Double cutting power.

ANSI B107.11M  
DIN 5238



ENERGY SAVING TYPE - LONG NOSE



PART NO.	SIZE INCH	L MM			G.W. (kg)
72401	6"	150	6	48	11.9
72402	8"	200	6	36	11.7

- High leverage.
- Double cutting power.

ANSI B107.13M  
DIN 5236



WIRE & CABLE CUTTING

PART NO.	SIZE INCH	L MM			G.W. (kg)
72501	6"	150	6	90	6.1
72502	8"	200	6	48	20.4
72503	10"	250	6	48	23.1

- For cutting vinyl coated or copper cables.



MULTIPURPOSE LONG NOSE

PART NO.	SIZE INCH	L MM			G.W. (kg)
72601	6"	150	6	90	6.2

ANSI B107.13M  
DIN 5236

