

Features

Unregulated Converters

- Low Cost 1W Converter
- Power Sharing on Dual Output Version
- Industry Standard Pinout
- 1kVDC or 2kVDC Isolation Options
- Optional Continuous Short Circuit Protected
- UL94V-0 Package Material
- Efficiency to 85 %

Description

The RB series DC/DC converter has been designed for isolating or converting DC power rails in general purpose applications. Although low cost, it does not compromise on features and offers 1kVDC or 2kVDC isolation, a -40°C to $+85^{\circ}\text{C}$ operating temperature range and optional continuous short circuit protection.

Selection Guide

Part Number		Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max Capacitive Load ⁽¹⁾
SIP 7	(2kV)					
RB-xx3.3S	(H)	3.3, 5, 12, 15, 24	3.3	303	75	2200 μF
RB-xx05S	(H)	3.3, 5, 12, 15, 24	5	200	70-78	1000 μF
RB-xx09S	(H)	3.3, 5, 12, 15, 24	9	111	70-78	1000 μF
RB-xx12S	(H)	3.3, 5, 12, 15, 24	12	84	78-80	470 μF
RB-xx15S	(H)	3.3, 5, 12, 15, 24	15	66	80-84	470 μF
RB-xx24S	(H)	3.3, 5, 12, 15, 24	24	42	74-85	220 μF
RB-xx3.3D	(H)	3.3, 5, 12, 15, 24	± 3.3	± 152	70	$\pm 1000\mu\text{F}$
RB-xx05D	(H)	3.3, 5, 12, 15, 24	± 5	± 100	70-78	$\pm 470\mu\text{F}$
RB-xx09D	(H)	3.3, 5, 12, 15, 24	± 9	± 56	76-79	$\pm 470\mu\text{F}$
RB-xx12D	(H)	3.3, 5, 12, 15, 24	± 12	± 42	78-82	$\pm 220\mu\text{F}$
RB-xx15D	(H)	3.3, 5, 12, 15, 24	± 15	± 33	80-84	$\pm 220\mu\text{F}$
RB-xx24D	(H)	3.3, 5, 12, 15, 24	± 24	± 21	80-84	$\pm 100\mu\text{F}$

xx = Input Voltage. Other input and output voltage combinations available on request.

* add Suffix "P" for Continuous Short Circuit Protection, e.g. RB-0505S/P, RB-0505S/HP

Specifications (measured at $T_A = 25^{\circ}\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	$\pm 10\%$	
Output Voltage Accuracy	$\pm 5\%$	
Line Voltage Regulation	1.2%/1% of V_{in} typ.	
Load Voltage Regulation (10% to 100% full load)	3.3V output type	20% max.
	5V output type	15% max.
	9V, 12V, 15V, 24V output types	10% max.
Output Ripple and Noise (20MHz limited)	Single output types	100mVp-p max.
	Dual output types	$\pm 75\text{mVp-p}$ max.
Operating Frequency	50kHz min. / 100kHz typ. / 105kHz max.	
Efficiency at Full Load	70% min. / 80% typ.	
Minimum Load = 0%	Specifications valid for 10% minimum load only.	
Isolation Voltage	(tested for 1 second)	1000VDC
	(rated for 1 minute)	500VAC / 60Hz
Isolation Voltage	H-Suffix	2000VDC
	H-Suffix	1000VAC / 60Hz
Isolation Capacitance	20pF min. / 75pF max.	
Isolation Resistance	10 $\text{G}\Omega$ min.	
Short Circuit Protection	1 Second	
P-Suffix	Continuous	
Operating Temperature Range (free air convection)	-40°C to $+85^{\circ}\text{C}$ (see Graph)	
Storage Temperature Range	-55°C to $+125^{\circ}\text{C}$	

ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM

1 Watt

SIP7


Single & Dual Output



EN-60950-1 Certified
UL-60950-1 Certified

RB

Derating-Graph (Ambient Temperature)



Refer to Application Notes



www.recom-electronic.com

Specifications - continued



Relative Humidity	95% RH		
Package Weight	2.2g		
Packing Quantity	25 pcs per Tube		
MTBF (+25°C)	} <i>Detailed Information see Application Notes chapter "MTBF"</i>	using MIL-HDBK 217F	1012 x 10 ³ hours
(+85°C)		using MIL-HDBK 217F	151 x 10 ³ hours

Typical Characteristics - Single Output



RB-xx05S





RB-xx09S



RB-xx12S




RB-xx15S




Typical Characteristics - Dual Outputs


RB-xx05D




RB-xx12D



RB-xx09D



RB-xx15D



Notes


Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

Certifications


CB Test Report	Report: US/15348/UL	IEC 60950-1:2005 2nd Ed.	UL General Safety	Report: E322406	UL
60950-1 1st Ed.	EN General Safety	Report: PS-R7219C1	EN60950-1:2001 + A11:2004		

Package Style and Pinning (mm)


7 PIN SIP Package





Single Output



Dual Output



Recommended Footprint Details



Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
4	NC	-Vout
5	-Vout	Com
6	+Vout	+Vout

NC = No Connection
XX.X ± 0.5 mm
XX.XX ± 0.25 mm