

Data Sheet

FLEXIBLE MAGNET 3 WATT INSPECTION TORCH

RS Stock No. 742-2823



Sizes:

Torch Overall Length (mm): 645 Flexible Shaft Included
Diameter (Ø mm): Head 17 X Barrel 36.5

Batteries Inserted: 3 X AA

Batteries Supply: Included

Weight (gm), Torch Only: 244

Magnet (Ø mm): Base 27 X 6, Head 12 X 6

Colour:

Metal Pewter Anodized Colour

Marking:

RS Laser Engraved Logo on Torch

Materials/Parts:

Case: 6463 Aluminium Alloy

Lens: Durable Optic Glass

LED: NICHIA NCSW119 High Power LED

Package: Folded PVC Blister with RS Card Inserted

Magnet:: Rare Earth, Steel

Features:

- 3-Position Barrel Push Button Switch (100%-50%-Off)
- Power Indicator on Hand Grip; Turns from GREEN to RED when Battery Power Is 20% Less
- NICHIA NCSW119 Lumen Output: 250 Lumens at Full Power Position; 125 Lumens at 50% Power Position
- Functioned by 3 X AA Batteries
- Battery Run Time: 10-12 hours (100% to 10%) at Full Power; 20-24 Hours at 50% Power
- Strong Magnet Installed on Torch Front as Necessary (Stored in Tail Cap when not in Use)
- Strong Magnet (4000 Gauss) Installed on Tail Cap Base
- Corrosion Resistant and Shock Proof

