



Duo ground blocks with tension spring connection



0344 Ex II 2GD IM2

Ex e I/II

EN 60 947-7-2:2002

UL ratings field/factory wiring

CSA ratings

PTB 04 ATEX 1051 U1) EN 60 079-0/EN 60 079-7

Width Wire strip length

Approvals

WKFN 2,5 SL/35

fine-stranded solid V A
 0.13–2.5 mm² 0.13–4 mm² 800 V/8 kV/3⁴⁾ 3)
 No. 22-12 AWG 600 V
 No. 24-12 AWG 600 V
 0.2–2.5 mm² 0.13–4 mm²
 5 mm 11 mm



WKFN 2,5 D1/2/SL/35

fine-stranded solid V A
 0.13–2.5 mm² 0.13–4 mm² 800 V/8 kV/3⁴⁾ 3)
 No. 22-12 AWG 600 V
 No. 24-12 AWG 600 V
 0.2–2.5 mm² 0.13–4 mm²
 5 mm 11 mm



Ground block	green/yellow	Type	Part No.	Std. Pack	Type	Part No.	Std. Pack
		WKFN 2,5 SL/35	56.703.9055.0	100	WKFN 2,5 D1/2/SL/35	56.703.9355.0	100
Accessories							
1. Mounting rail 35, 7.5 mm high	L = 2 m	35x27x7,5 EN 60715	98.300.0000.0	1	35x27x7,5 EN 60715	98.300.0000.0	1
Mounting rail 35, 15 mm high	L = 2 m	35x27x15 EN 60715	98.370.0000.0	1	35x27x15 EN 60715	98.370.0000.0	1
2. End clamp TS 35, with screw	8 mm wide	9708/2 S35	Z5.522.8553.0	100	9708/2 S35	Z5.522.8553.0	100
End clamp TS 35, without screw	8 mm wide	WEF 1/35	Z5.523.9353.0	100	WEF 1/35	Z5.523.9353.0	100
3. End plate	gray	APFN 2,5	07.312.6755.0	10	APFN 2,5 D1/2	07.312.6955.0	10
	blue						
4. Partition plate	gray						
5. Cross connector	2 pole						
insulated (jumper bar)	3 pole						
	4 pole						
	5 pole						
	6 pole						
	7 pole						
	8 pole						
	9 pole						
	10 pole						
6. Wire entry guide	0.13–0.2 mm ²	LELN 2,5/1 WEISS	05.564.3755.0	100	LELN 2,5/1 WEISS	05.564.3755.0	100
	0.25–0.5 mm ²	LELN 2,5/2 GRAU	05.564.3855.0	100	LELN 2,5/2 GRAU	05.564.3855.0	100
	0.75–1.0 mm ²	LELN 2,5/3 SCHWARZ	05.564.3955.0	100	LELN 2,5/3 SCHWARZ	05.564.3955.0	100
7. Cover with warning symbol over 4 blocks		ADFN 2,5/4 GELB	04.343.8353.8	10	ADFN 2,5/4 GELB	04.343.8353.8	10
8. Marking tag carrier, 2-fold							
9. Test adapter, modular							
10. Test plug							
11. Screwdriver, uninsulated		DIN 5264 B 0,6x3,5	06.502.4000.0	5	DIN 5264 B 0,6x3,5	06.502.4000.0	5
Screwdriver, uninsulated, MINI		DIN 5264 B 0,6x3,5 M	06.502.5000.0	10	DIN 5264 B 0,6x3,5 M	06.502.5000.0	10
Marking accessories see page 77–81							

¹⁾ Follow the Ex installation instructions.

⁴⁾ Ratings to adjacent feed-through blocks of the same series and size.

³⁾ For the current-carrying capabilities of the mounting rails see flyer **facts & DATA**.