

Data Sheet

> Goliath 250 Plus

Schneider Electric
United Kingdom




Product Description

IP rated work light with low consumption 55W 2D lamps with High Frequency electronic ballast

Features

- High impact resistant polycarbonate construction
- Virtually shatter proof Case and Lens
- Light remains cool avoiding fire hazard
- 5m of rubberised Cable & Flexible hanging strap
- Handle with several predefined position
- Silent Operation due to High Frequency Electronic Ballast
- 55W lamp provides light out equivalent of 500W Halogen Lamp
- IP54 Protected against Dust and splashing of water with sockets closed or in use
- Rear On/Off Switch

Technical Specification

- **Product compliance:** GS Mark Approved
EN 60598-1 : Luminaires Part 1 : General requirements & test
EN 60598-2-4 : Portable general purpose luminaire
EN 55015, EN61000-3-2, EN61000-3-3, EN61547 : EMC
- **Lamp Type** 55W GRY10q-3 (3500K) 4 pin 2D
- **Lamp Lumens** 4000 Lumens @ 30 C
- **Lamp Life** 10,000 Hours
- **Lamp CRI** Ra 82
- **Light output** Measured at 1m distance : 1700lux(approx)
Measured at 3m distance : 200lux(approx)
- **Maximum Load** 16A (Total Circuit Amps)
- **Rated Voltage** 230-240V
- **Plug** 13A BS 1363 approved
- **Sockets** 2 socket outlets with Earth which correspond to IEC 60083
- **Cable:** HO7RN-F3 X 1.5mm
- **Daisy Chain:** 4 Units (Max)
- **Markings**  Rough Service Luminaire
- **Dimensions(approx)** Height =316mm
Width = 316mm
Depth = 91mm
Weight =3.3Kg
- **Ambient Working Temperature** -15C to 50C(Note : temperatures higher than 35C will reduce lifetime)

RoHS & REACH approved

We accept no liability for printing errors and reserve the right to change the specifications without notice