

## Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883



### Range features

- Single pin-base compact lamps, suitable for wide range of applications
- Excellent colour rendering - (CRI=85)
- For use with magnetic ballast
- Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K)
- Average rated life: 10000 hours



### PRODUCT OVERVIEW

Ordering number	0025883
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	NO
Cap/Base	G23
Type	Lynx S
EAN code	5410288258836
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	900
Efficacy (Rated) (lm/w)	76
Watt (Nominal) (W)	11
Voltage (V)	91

## Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

### DATA TABLE

#### General data

<b>Ordering number</b>	0025883
<b>Dry applications use only</b>	yes
<b>Technology</b>	Compact Fluorescent
<b>Average life (Nominal) (h)</b>	10000
<b>Energy class</b>	A
<b>Average life (Rated) (h)</b>	10000
<b>Lamp shape</b>	Stick
<b>Lamp finish</b>	frosted
<b>Dimmable</b>	NO
<b>Cap/Base</b>	G23
<b>Type</b>	Lynx S
<b>EAN code</b>	5410288258836
<b>E-number FI</b>	4944082
<b>E-number SE</b>	8357264
<b>Long description</b>	Single pin-base compact lamps, suitable for wide range of applications. Excellent colour rendering - (CRI=85). For use with magnetic ballast. Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K). Average rated life: 10000 hours
<b>Product name</b>	SA LYNX-S 11W/827 G23 SLV 10
<b>Lamp mercury content (mg)</b>	< 2.50 mg
<b>Starting time (max) (s)</b>	10 Sec
<b>Control gear required</b>	Yes
<b>Fixture rating</b>	Open
<b>IEC Reference</b>	IEC 60901
<b>IEC Reference 2</b>	IEC 61199
<b>IEC Reference 3</b>	IEC 60921
<b>Intended purpose</b>	General lighting
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	10
<b>Rated survival factor at 2000 h 50Hz</b>	0.98
<b>Rated survival factor at 4000 h 50Hz</b>	0.9
<b>Rated survival factor at 6000 h 50Hz</b>	0.7
<b>Rated survival factor at 8000 h 50Hz</b>	0.5
<b>Rated survival factor at 12000 h 50Hz</b>	0.62

## Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

### Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	900
Luminous flux (Nominal) (lm)	900
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.85
Rated lumen maint. factor at 4000 h 50Hz	0.78
Rated lumen maint. factor at 6000 h 50Hz	0.76
Rated lumen maint. factor at 8000 h 50Hz	0.75
Rated lumen maint. factor at 12000 h 50Hz	0.8

### Electrical data

kWh per 1000 hours burning time	14
Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.	76
Efficacy (Rated) (lm/w)	76
Watt (Nominal) (W)	11
Watt (Rated) - High frequency (W)	50
Watt (Rated) (W)	11.8
Voltage (V)	91
Ignition voltage (V)	186
Current (A)	0.155

### Physical data


Weight (kg)	0.04
Length base to base (mm) - A	236
Lamp Length (mm) - C/L	213
Max. Lamp Diameter (mm) - D	32.5
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	2.20 x 3.80 x 22.90
Inner package dimensions (L x W x H) (cm)	12.40 x 9.00 x 24.80
Inner package net weight (kg)	0.38
Outer package dimensions (L x W x H) (cm)	45.50 x 26.90 x 26.50

## Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

### TECHNICAL DRAWINGS



### ENERGY LABEL

