

Contact insert - RC-12S1N8D0000 - 1599343

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Contact insert, Number of positions: 12, Type of contact: Socket, Crimp connection



The figure shows the 6-pos. product version



Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 225465
Weight per Piece (excluding packing)	10.7 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Insertion/withdrawal cycles mechanical	50
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Socket
Number of positions	12
Contact diameter of power contacts	1 mm
Litz wire cross section of power contacts min.	0.14 mm ²
Litz wire cross section of power contacts max.	0.56 mm ²
Nominal current per power contact at 25°C	8 A

Material

Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating

Contact insert - RC-12S1N8D0000 - 1599343

Technical data

Specifications according to DIN EN 61984:2001

Nominal / operating voltage of power contacts	150 V
Rated surge voltage of power contacts	1.5 kV
Surge voltage category of power contacts	II
Pollution degree of power contacts	3
Surge voltage category of signal contacts	II
Pollution degree of signal contacts	3

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM


ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Drawings

Schematic diagram



Schematic diagram



Contact insert - RC-12S1N8D0000 - 1599343

Schematic diagram

