



OFF-STATE (LEAKAGE) CURRENT	<10 μA
NO-LOAD CURRENT	5.5-9.5 mA
TIME DELAY BEFORE AVAILABILITY	≤8 ms
POWER-ON EFFECT PROTECTION	INCORPORATED
REVERSE POLARITY PROTECTION	INCORPORATED
WIRE-BREAK PROTECTION	INCORPORATED
PROTECTION AGAINST TRANSIENTS	2 kV, 1 ms, 1 kΩ
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)
ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67
SHOCK	30 g, 11 ms
VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)
LED FUNCTION	RED: OUTPUT ENERGIZED
SENSING RANGE	15 mm = .591" (NOMINAL)
SWITCHING FREQUENCY	500 Hz
REPEATABILITY	≤2% of RATED OPERATING DISTANCE
EMBEDDABLE (SHIELDED)	NO

MATERIAL <b>BRASS BARREL</b>		3RD ANGLE PROJECTION 		<b>TURCK INC</b> 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224	
FINISH <b>COPPER/NICKEL/ CHROME PLATING</b>					
DRWN SMW	DATE 3/18/87	PART NO. <b>Ni15-G30-AN6X</b>			
CHKD	DATE	SIZE <b>B</b>		ID NO. <b>4647700</b>	REV <b>C</b>
TMI		SCALE NONE		BMPC-DC\4647700	SHEET OF

C	SEE REVISION DOCUMENT 4647600	SWC	8/1/94		
REV	DESCRIPTION	DRFT	DATE	CHKD	
REVISIONS					

DIMENSIONS ARE IN INCHES  
mm