


PERMANENT MAGNETS

HSI PART#	M-01	M-02	M-03	M-04	M-05	M-06	M-08	M-16
Length	.500+/-0.010 (12.7)	.750+/-0.015 (19.0)	.975+/-0.030 (24.8)	1.00+/-0.030 (25.4)	1.40+/-0.020 (35.6)	.410+/-0.005 (10.2)	.200+/-0.005 (5.1)	.375+/-0.010 (9.5)
Width	.062+/-0.005 (1.6)	.125+/-0.005 (3.2)	.180+/-0.007 (4.6)	.250+/-0.015 (6.4)	.250 Dia+/- .010 (6.3)	.100 Dia+/- .005 (2.5)	.250 Dia+/- .005 (6.4)	.150+/-0.010 (3.8)
Height	.062+/-0.005 (1.6)	.125+/-0.005 (3.2)	.180+/-0.007 (4.6)	.250+/-0.015 (6.4)	Cylinder	Cylinder	Cylinder	.375+/-0.010 (9.5)
GAUSS**	475	975	950	1000	780	725	3100	570
MAGNET MATERIAL	SINTERED ALNICO 5	SINTERED ALNICO 5	SINTERED ALNICO 5	SINTERED ALNICO 5	SINTERED ALNICO 5	SINTERED ALNICO 5	NE027	CERAMIC VIII



[Hermetic Switch, Inc.](http://www.hsi.com)

Tel. 405-224-4046 Fax 405-224-9423