

The testo 476 Pocket Strobe™ hand-held stroboscope measures and checks rotation and vibration movements. It facilitates the measurement of very small objects or in hard-to-access places.

The energy optimised switching electronics and light-intensive xenon flash lamp facilitate a high light intensity (approx. 800 lux).

- **High setting accuracy and stability thanks to dynamic setting dial**
- **High light intensity due to energy optimised switching electronics and powerful xenon flash lamp**
- **Powerful rechargeable battery pack for min. 1 hour operation time over the frequency range**
- **Automatic trigger to synchronize flash sequence**


Kit

testo 476, Pocket Strobe™ hand-held stroboscope incl. transport case, recharger with 4 country adapters and trigger signal connector

Part no. 0563 4760



rpm measurement in a turbine, for example



Measure the speed in rapid stroke machines, for example

[illegible]

testo 476, The Affordable Kit



testo 476, Pocket Strobe™
hand-held stroboscope incl.
transport case, recharger with
4 country adapters and trigger
signal connector

Part no. 0563 4760

Meas. range	+30...+12500 rpm	Oper. temp.	0... +40 °C
		Weight	465 g
Accuracy ± 1 digit	±0.01% of mv (+30... +12500 rpm)	Dimensions	240x65x50 mm
		Warranty	2 years
Resolution	1 rpm (+30... +12500 rpm)	Display: 5 digit LCD display	
		Illumination: 800 Lux at distance of approx. 20 cm	
		Flash energy: max. 150 mJ	
		Operating time: 1h at 30 to 12,500 rpm and 23°C (typically)	