

## Cable - VIP-CAB-FLK26/0,14/1,5M - 2318648

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled round cable with two molded 26-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 1.5 m




The figure shows the 50-pos. product version

### Why buy this product

- Available in any choice of length
- 26 to 50-pos.
- Individual serial number
- Connector according to IEC 60603-13
- 1:1 connection



### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 046356 311922 |
| Weight per Piece (excluding packing) | 189.5 g   |
| Custom tariff number                 | 85444290  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### General

|   |                      |
|---|----------------------|
| Nominal voltage $U_N$                         | < 50 V AC            |
|   | 60 V DC              |
| Max. current carrying capacity per path       | 1 A                  |
| Max. conductor resistance                     | 0.16 $\Omega/m$      |
| Length of cable                               | 1.5 m                |
| Single wire, cross section                    | 0.14 mm <sup>2</sup> |
| AWG   | 26                   |
| Conductor construction: Number of litz wires: | 7                    |

# Cable - VIP-CAB-FLK26/0,14/1,5M - 2318648

## Technical data

### General

|                        |   |
|------------------------|---|
| Single wire, material  | Cu tin-plated                                       |
| External diameter      | 8.3 mm  |
| Cable, preassembly     | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding              | no  |
| Outer sheath, material | PVC   |
| External sheath, color | Gray RAL 7035                                       |

### Environmental conditions

|   |                             |
|---|-----------------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C            |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C            |
| Flame resistance                        | IEC 60332-1                 |
| Resistance to oil                       | UL 1581                     |
| Gasoline resistance                     | Against occasional splashes |

### Connector, module side

|                     |                                |
|---------------------|--------------------------------|
| Number of positions | 26                             |
| Connectors          | IDC/FLK socket strip (2.54 mm) |
| Number of plugs     | 1                              |

### Connector, controller side

|                     |                                |
|---------------------|--------------------------------|
| Number of positions | 26                             |
| Connectors          | IDC/FLK socket strip (2.54 mm) |
| Number of plugs     | 1                              |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27249205 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 6.01 | 26121620 |
|-------------|----------|

# Cable - VIP-CAB-FLK26/0,14/1,5M - 2318648

## Classifications

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11     | 26121620 |
| UNSPSC 12.01  | 26121620 |
| UNSPSC 13.2   | 26121620 |

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

UL Recognized

cUL Recognized

EAC

cULus Recognized

## Drawings

## Cable - VIP-CAB-FLK26/0,14/1,5M - 2318648

Dimensioned drawing

