

# Multiple Outlet Strips

## Medical and Dental Grade Plug-In Outlets — ULM Series

The Medical/Dental Grade Plug-In Outlet Center with Four Outlets is ideal for use in a wide variety of settings, including relay racks and cabinets, laboratories, workshops, classrooms and offices. Suitable for use where Article 517 of the NEC requires Hospital Grade Outlets.

### ULM Series

Stock No.	Mfr.'s Type	No. of Outlets	Master Switch/Pilot Light	Dimensions L x W x H (Inches)	Cord Length (Feet)	Shipping Weight (Lbs.)	EACH	
							1-4	5-9
70091549	ULM4-6	4	No	10 <sup>3</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.00	87.64	83.11
70091550	ULM4-15	4	No	10 <sup>3</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.00	96.90	91.88
70091559	ULM6-6	6	No	13 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.25	114.58	109.29
70091560	ULM6-15	6	No	13 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.25	120.41	118.63
70271195	ULM620-6	6	No	10 <sup>3</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	—	263.41	—
70271196	ULM620-15	6	No	10 <sup>3</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	—	298.70	—



- Features:**
- ▶ cTUVus Listed as Medical Electrical Equipment
  - ▶ Suitable for Use Where Article 517 of the NEC Requires Hospital Grade Outlets
  - ▶ Receptacle Center-to-Center Electrical Rating 12 A, 125 V
  - ▶ Resettable Circuit Breaker That Provides Overload Protection
  - ▶ Two-Year Warranty
  - ▶ 20 A Version for Meeting Increasing Power Demands of Electrical Equipment
  - ▶ 16 A Electrical Rating

## Compact Ready-to-Use "Plug-In Outlet Center" Units

Designed to provide power where space is limited. Gray aluminum housing, except where noted.

Stock No.	Mfr.'s Type	No. of Outlets	Master Switch/Pilot Light	Dimensions L x W x H (Inches)	Cord Length (Feet)	Shipping Weight (Lbs.)	EACH	
							1-14	15-24
70091695	UL100BC	5	No	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.50	25.86	24.84
70091696	UL100BD	5	No	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.50	31.33	30.60
70091691	UL101BC	4	No	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.50	24.35	23.40
70091692	UL101BD	4	No	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.50	30.53	29.36
70091697	UL104BC	4	Yes	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.50	27.37	26.31
70091698	UL104BD	4	Yes	9 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.50	35.96	34.51
70091699	UL204BC	7	Yes	13 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.75	38.65	37.10
70091700	UL204BD	7	Yes	13 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.75	44.86	43.06
70091701	UL205BC	8	No	13 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.75	35.56	33.87
70091702	UL205BD	8	No	13 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.75	42.57	40.86
70091703	UL207BC	6	Yes	12 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.75	34.68	33.08
70091704	UL207BD	6	Yes	12 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.75	42.46	40.82
70091730	UL210BC*	10	Yes	13 x 3 <sup>1</sup> / <sub>2</sub> x 2	6	2.25	48.82	46.95
70091778	UL210BD*	10	Yes	13 x 3 <sup>1</sup> / <sub>2</sub> x 2	15	3.25	54.95	53.37
70091758	UL218BC	8	Yes	15 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.00	45.82	43.26
70091759	UL218BD	8	Yes	15 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.00	43.16	41.48
70091516	UL1090BC†	4	No	16 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.00	32.58	31.27
70091517	UL1090BD†	4	No	16 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.00	41.41	39.76
70091761	P6‡	6	Yes	12 x 2 <sup>1</sup> / <sub>2</sub> x 1 <sup>5</sup> / <sub>8</sub>	6	1.30	13.25	12.53
70091750	P6-15‡	6	Yes	12 x 2 <sup>1</sup> / <sub>2</sub> x 1 <sup>5</sup> / <sub>8</sub>	15	2.20	17.38	16.46
70091755	R610**	6	Yes	12 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.00	30.02	27.27
70091756	R612**	6	Yes	12 <sup>1</sup> / <sub>4</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.00	28.55	26.77
70091772	IEC5•	5	No	11 x 2 x 1 <sup>3</sup> / <sub>4</sub>	•	1.25	58.11	55.87

\*Model is Putty White and features keyhole mounting (mounting center-9<sup>1</sup>/<sub>16</sub>). †Receptacles spaced 90° to accommodate transformers. ‡Model has putty white plastic housing and features keyhole mounting (mounting center-9<sup>1</sup>/<sub>16</sub>). •Model is equipped with IEC 320 plug and receptacles. User must provide appropriate international adapter power cord equipped with IEC 320 connector. \*\*R610 and R612 have Snap-on/Slide-off mounting. •RoHS compliant.




- Features:**
- ▶ Grounded Outlets
  - ▶ Built-In Circuit Breakers
  - ▶ Snap-On, Adjustable Mounting Clips
  - ▶ Maximum Rating of 15 A, 120 V
  - ▶ Grounded Electrically and Mechanically

## Industrial Ready-to-Use "Plug-In Outlet Center" Units

Rugged aluminum housing is ideal for tough work environments. Multiple receptacles provide power where it is needed most.

Stock No.	Mfr.'s Type	No. of Outlets	Master Switch/Pilot Light	Dimensions L x W x H (Inches)	Cord Length (Feet)	Shipping Weight (Lbs.)	EACH	
							1-14	15-24
70091675	UL300BC	8	Yes	24 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.50	50.75	48.79
70091676	UL300BD	8	Yes	24 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	3.25	60.08	57.77
70271211	UL309BC	9	Yes	36 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	—	139.18	—
70271212	UL309BD	9	Yes	36 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	—	152.77	—
70091716	UL401BC	8	Yes	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	3.60	58.80	57.91
70091717	UL401BD	8	Yes	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	4.60	66.65	64.09
70091769	UL402BC	16	Yes	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	3.70	74.38	71.50
70091770	UL402BD	16	Yes	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	4.70	79.46	76.39
70091677	UL403BC	8	No	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	3.60	55.46	53.32
70230913	UL403BD	8	No	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	4.60	57.62	55.39
70091771	UL404BC	16	No	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	3.70	74.37	71.49
70091762	UL404BD	16	No	48 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	4.70	79.46	76.39
70091773	UL2063BC	24	No	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	5.10	86.98	83.50
70091774	UL2063BD	24	No	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	6.20	92.08	88.41
70091705	UL2064BC	12	Yes	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	4.90	63.57	61.01
70091706	UL2064BD	12	Yes	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	5.50	71.37	68.08
70091707	UL2065BC	24	Yes	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	5.10	89.49	86.02
70091757	UL2065BD	24	Yes	72 x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	6.20	94.56	90.91



- Features:**
- ▶ Grounded Outlets
  - ▶ Silver Gray Aluminum Housing
  - ▶ Built-In Circuit Breakers
  - ▶ Snap-On, Adjustable Mounting Clips
  - ▶ Maximum Rating of 15 A, 120 V
  - ▶ Grounded Electrically and Mechanically
- Applications:**
- ▶ Workbenches
  - ▶ Electronic Cabinets
  - ▶ Computer Rooms
  - ▶ POP Displays
  - ▶ Exhibits

## Mounting Ear Models

Each unit is 100% quality inspected to meet electrical codes and industrial standards. Mounting ear models contain "UL Listed" or "UL Recognized" components.

Stock No.	Mfr.'s Type	No. of Outlets	Master Switch/Pilot Light	Dimensions L x W x H (Inches)	Cord Length (Feet)	Shipping Weight (Lbs.)	EACH	
							1-14	15-24
70091766	L10316	4	No	8 <sup>5</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	1.5	76.75	74.28
70091749	L10317	4	No	8 <sup>5</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.0	69.16	66.07
70091723	L10318	7	Yes	14 <sup>3</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.0	65.52	—
70091767	L10319	7	Yes	14 <sup>3</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.5	94.20	87.27
70091760	L10320*	9	No	13 <sup>3</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	4.0	90.01	85.86
70091724	L10309	6	Yes	13 <sup>1</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	6	2.0	89.61	85.35
70091725	L10323	6	Yes	13 <sup>1</sup> / <sub>8</sub> x 2 x 1 <sup>3</sup> / <sub>4</sub>	15	2.5	94.44	91.38
70230914	C10221	12	Yes	48 x 1 <sup>1</sup> / <sub>2</sub> x 1 <sup>3</sup> / <sub>16</sub>	6	5.5	88.49	85.76
70091768	C10222	12	Yes	48 x 1 <sup>1</sup> / <sub>2</sub> x 1 <sup>3</sup> / <sub>16</sub>	15	6.0	87.33	—

\*No built-in circuit breaker.



- Features:**
- ▶ Maximum Rating of 15 A, 120 V
  - ▶ Built-In Circuit Breakers
  - ▶ Aluminum Silver Gray Housing
  - ▶ Snap-On, Adjustable Mounting Clips