



### Rubber Tubing, Chloroprene

- Helsyn H

The chloroprene tubings (H) are ideally suited to rigorous environments such as aerospace, mass transit and defence markets.

As the material is highly elastic, it's original size can be expanded 500% on application and 200% in continuous use.

To save time and effort when fitting the tubing, try the HellermannTyton K, S and SS three prong tools (see Chapter 6.3) and the Hellerine lubricant (see Chapter 2.3), which are specially designed for use with HellermannTyton chloroprene tubing.

#### Features and Benefits

- Highly elastic Chloroprene tubing
- Withstands up to 120°C intermittent temperature
- Covers many cable diameters with one size
- Available in cut lengths



*H rubber tubing is highly flexible and easy to apply.*

<b>MATERIAL</b>	Chloroprene (CR)
<b>Operating Temperature</b>	-65 °C to +95 °C, intermittent 120 °C
<b>Flammability</b>	UL94 HB
<b>Specifications</b>	BS-3858 Type 1, BS-4G-198 Part 1 Type 1, DEF STAN 59-15 D2, IEC 684-3-116



*Chloroprene tubing*

TYPE	Supplied Ø D min.	Wall (WT)	Length (L)	Pack Cont.	Colour	Article-No.
H12	1.2	0.70	20.0	1,000 pcs.	Black (BK)	600-01520
H15	1.5	0.80	20.0	1,000 pcs.	Black (BK)	600-01600
H20	2.0	0.80	20.0	1,000 pcs.	Black (BK)	600-01700
H30	3.0	0.80	25.0	1,000 pcs.	Black (BK)	600-01841
H50	5.0	1.00	25.0	1,000 pcs.	Black (BK)	600-01982
H75	7.5	1.30	25.0	1,000 pcs.	Black (BK)	600-02063
H100	10.0	1.50	25.0	1,000 pcs.	Black (BK)	600-02105
H150	15.0	1.70	25.0	1,000 pcs.	Black (BK)	600-02155

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.