

# CAD50GD

contactor TeSys CAD-50 - 5 NO -  
instantaneous - 10 A - 125 V DC



## Main

Range of product	TeSys D
Product or component type	Auxiliary contactor
Device short name	CAD
Contact application	Control circuit
Utilisation category	DC-13
Control circuit type	DC
Coil type	Standard
Suppressor technology	Bidirectional peak limiting diode
Pole contact composition	5 NO
Control circuit voltage	125 V DC
Connections - terminals	Screw-clamp terminal 1 1...4 mm <sup>2</sup> flexible without Screw-clamp terminal 2 1...4 mm <sup>2</sup> flexible without Screw-clamp terminal 1 1...4 mm <sup>2</sup> flexible with Screw-clamp terminal 2 1...2,5 mm <sup>2</sup> flexible with Screw-clamp terminal 1 1...4 mm <sup>2</sup> solid without Screw-clamp terminal 2 1...4 mm <sup>2</sup> solid without

## Complementary

Contact operation	Mechanically linked IEC 60947-5-1
Control circuit voltage limits	0.1...0.25 U <sub>c</sub> drop-out 0.7...1.25 U <sub>c</sub> operational
Time constant	28 ms
[U <sub>i</sub> ] rated insulation voltage	600 V UL 600 V CSA 690 V III IEC 60947-5-1 3
[U <sub>imp</sub> ] rated impulse withstand voltage	6 kV IEC 60947
Tightening torque	1,7 N.m screw-clamp terminal
[U <sub>e</sub> ] rated operational voltage	<= 690 V DC
[I <sub>th</sub> ] conventional free air thermal current	10 A ≤ 60 °C
I <sub>rms</sub> rated making capacity	250 A <= 690 V DC IEC 60947-5-1
Permissible short-time rating	100 A 1 s 120 A 500 ms 140 A 100 ms
Associated fuse rating	10 A gG <= 690 V IEC 60947-5-1
Inrush power in W	5,4 W 20 °C
Hold-in power consumption in W	5,4 W 20 °C
Mechanical durability	30000000 cycles
Operating rate	3 cyc/s 20 °C
Operating time	20 ms +/- 20 % coil de-energisation and NO opening 25 ms +/- 20 % coil de-energisation and NC closing 55 ms +/- 15 % coil energisation and NC opening 63 ms +/- 15 % coil energisation and NO closing
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1,5 ms on energisation between NC and NO contacts 1,5 ms on de-energisation between NC and NO contacts
Insulation resistance	> 10 MOhm
Height	77 mm
Width	45 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Depth	95 mm
Product weight	0,58 kg

## Environment

Standards	BS 4794 EN 60947-5 IEC 60947-5-1 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x VDE 0106
Protective treatment	TH IEC 60068
Ambient air temperature for operation	-40...70 °C at U <sub>c</sub> -5...60 °C at 0.8...1.1 U <sub>c</sub>
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without
Shock resistance	10 gn control relay open 15 gn control relay closed
Vibration resistance	2 gn control relay open 5...300 Hz 4 gn control relay closed 5...300 Hz
RoHS EUR conformity date	0914
RoHS EUR status	Compliant