



NSL-19M51


Plastic Encapsulated

Description

The NSL-19M51 is a CdS photoconductive cell on a TO-18 ceramic plastic encapsulated for moisture resistance.

Absolute Maximum Ratings

Operating & Storage Temp -60°C to +75°C
 Power Dissipation @ 25°C (1) 50 mW
 Voltage (peak AC or DC) 100 V



Electrical Characteristics ($T_A=25^\circ\text{C}$, source at 2854°K)(2)

Symbol	Parameter	Min	Typ	Max.	Units	Test Conditions
R_L	Light Resistance	20		100	$K\Omega$	10 lux
			5		$K\Omega$	100 lux
R_D	Dark Resistance	20			$M\Omega$	10 sec after removal of light
λ_p	Peak spectral wavelength		550		nm	
Γ	Gamma		0.7			1 - 10 Lux
Γ	Gamma		0.7			10 - 100 Lux

Specifications subject to change without notice

102082 REV 3

Notes: (1) derate linearly to 0 at 75°C

(2) cells to be light adapted at 30 to 50 Ftc for 16 hrs minimum prior to electrical tests

5200 St. Patrick St., Montreal
 Que., H4E 4N9, Canada
 Tel: 514-768-8000
 Fax: 514-768-8889

The Old Railway, Princes Street
 Ulverston, Cumbria, LA12 7NQ, UK
 Tel: 01 229 581 551
 Fax: 01 229 581 554