


NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	03.22.04'
②	BACKGROUND FORMAT UPDATED	08.08.11'
③	ADD VSWR	08.27.13'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS
- 1.3 DC RESISTANCE: 75 OHMS±5%
- 1.4 POWER RATING: 2W
- 1.5 VSWR: 1.3 MAX. @300 MHz ③

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +70° C

11	INSULATION	TEFLON	1	NONE
10	BODY II	BRASS	1	SILVER 70 μ"MIN.
9	RESISTOR	2W-75Ω	1	NONE
8	BODY I	BRASS	1	SILVER 70 μ"MIN.
7	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD
6	WASHER	BRASS	1	SILVER 70 μ"MIN.
5	SPRING WASHER	SK-5	1	NICKEL
4	WASHER	BRASS	1	NICKEL
3	GASKET	SILICONE	1	RED
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	SILVER 70 μ"MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____

DATE: _____



DESCRIPTION		BNC STRAIGHT PLUG-JACK FEEDTHRU TERMINATION						
製圖	DRAWN	TOLERANCE	品名	13-58 T.G.S	日期	DATE	版次	REV.
	Yoko							
檢圖	CHECK	UNIT	單位	DWG.NO.	13-0565	SCALE	比例	3:1
	Ivan							
認定	APPROVAL	.XXX ±0.05	ANGLE	±5°				
	Angela							