


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	A	INITIAL RELEASE	16OCT2009	RC AH



NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm OR 1300 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2 RETURN LOSS ≥ 20 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
- 3 TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4 CABLE INFORMATION:
 - CORE DIAMETER: 62.5/125 μ m
 - OUTER JACKET DIAMETER: 0.9 mm
 - OUTER JACKET COLOUR: BLUE
 - OUTER JACKET MATERIAL: LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061301-Y	XY.0

Qty	Description	Item
1	TEST RESULT SHEET	-
1	LC CONNECTOR, ONE PIECE, MULTI MODE, BEIGE	2
L	FOCAB 0.9S 62.5/125, BLUE, LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: mm		CHK A. HENGELMOLEN 16OCT2009	NAME FIBER OPTIC PIGTAIL 0.9S LC/PC MULTI MODE 62.5/125	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 16OCT2009	SIZE A2 CAGE CODE 00779 DRAWING NO C=2061301 RESTRICTED TO -	
0 PLC \pm -		PRODUCT SPEC -	SCALE NTS SHEET 1 of 1 REV A	
1 PLC \pm -		APPLICATION SPEC -	CUSTOMER DRAWING	
2 PLC \pm -		WEIGHT -		
3 PLC \pm -				
4 PLC \pm -				
ANGLES \pm -				
FINISH -				