

NOTES:

1. SPECIFICATIONS:


STROKE:	3.25 IN. (82.5 mm)
LENGTH:	11.5 IN. (292 mm)
MAX. LENGTH:	15.0 IN. (381 mm)
HANDLE WIDTH:	8.0 IN. (203 mm)
WEIGHT:	4.4 LB. (2.0 kg)
MAX APPLIED STRAP TENSION:	2500 LB. (1134 kg)
MAX HANDLE FORCE:	46 LB. (20.9 kg)
COLOR:	BLUE

2. FEATURES:

- DROP FORGED BANDING TOOL WITH BUILT-IN CUTTER.
- ALL METAL PARTS ARE HEAT-TREATED.
- SCREW DRIVEN TENSION MECHANISM.
- ROTARY CUTTER.
- CUTTER HANDLE.

3. PANDUIT BT75SDT USES:

PANDUIT METAL BANDING SYSTEM: MS75.



DISCRETE LENGTHS:	
PART NUMBER	DESCRIPTION
MS4W75T30-01	4" (102 mm) DIA SINGLE LOOP, 2" (51 mm) DIA DOUBLE LOOP, 201SS
MS6W75T30-01	6" (152.4 mm) DIA SINGLE LOOP, 3" (76.2 mm) DIA DOUBLE LOOP, 201SS
MS8W75T30-01	8" (203 mm) DIA SINGLE LOOP, 4" (102 mm) DIA DOUBLE LOOP, 201SS
MS10W75T30-01	10" (254 mm) DIA SINGLE LOOP, 5" (127 mm) DIA DOUBLE LOOP, 201SS
MS12W75T30-01	12" (305 mm) DIA SINGLE LOOP, 6" (152.5 mm) DIA DOUBLE LOOP, 201SS
MS14W75T30-01	14" (356 mm) DIA SINGLE LOOP, 7" (178 mm) DIA DOUBLE LOOP, 201SS
MS18W75T30-01	18" (457 mm) DIA SINGLE LOOP, 9" (228.5 mm) DIA DOUBLE LOOP, 201SS
MS20W75T30-X1	20" (508 mm) DIA SINGLE LOOP, 10" (254 mm) DIA DOUBLE LOOP, 201SS
MS24W75T30-X1	24" (610 mm) DIA SINGLE LOOP, 12" (305 mm) DIA DOUBLE LOOP, 201SS
MSC4W75T30-01	4" (102 mm) DIA SINGLE LOOP, 2" (51 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC6W75T30-01	6" (152.4 mm) DIA SINGLE LOOP, 3" (76.2 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC8W75T30-01	8" (203.2 mm) DIA SINGLE LOOP, 4" (254 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC10W75T30-01	10" (254 mm) DIA SINGLE LOOP, 5" (127 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC12W75T30-01	12" (305 mm) DIA SINGLE LOOP, 6" (152.5 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC14W75T30-01	14" (356 mm) DIA SINGLE LOOP, 7" (178 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC18W75T30-01	18" (457 mm) DIA SINGLE LOOP, 9" (228.5 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC20W75T30-X1	20" (508 mm) DIA SINGLE LOOP, 10" (254 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
MSC24W75T30-X1	24" (610 mm) DIA SINGLE LOOP, 12" (305 mm) DIA DOUBLE LOOP, 201SS, POLYESTER COATED
COILS:	
PART NUMBER	DESCRIPTION
MSW75T30-CR1	3/4" (19 mm) X .030" (.76 mm) COIL, 201SS
MSW75T30-CRT1	3/4" (19 mm) X .030" (.76 mm) COIL, 201SS, REUSABLE TOTE
MSW75T30-CR6	3/4" (19 mm) X .030" (.76 mm) COIL, 316SS
MSW75T30-CRT6	3/4" (19 mm) X .030" (.76 mm) COIL, 316SS, REUSABLE TOTE
MSCW75T30-CR1	3/4" (19 mm) X .030" (.76 mm) COIL, 201SS, POLYESTER COATED
MSCW75T30-CRT1	3/4" (19 mm) X .030" (.76 mm) COIL, 201SS, POLYESTER COATED, REUSABLE TOTE
MSCW75T30-OR6	3/4" (19 mm) X .030" (.76 mm) COIL, 316SS, POLYESTER COATED
MSCW75T30-ORT6	3/4" (19 mm) X .030" (.76 mm) COIL, 201SS, POLYESTER COATED, REUSABLE TOTE
BUCKLES:	
PART NUMBER	DESCRIPTION
MSBW75-C1	BUCKLE 201SS
MSBW75-C6	BUCKLE 316SS
MSCBW75-C1	BUCKLE COATED 201SS

TOOL DIV.
ENGINEERING DEPT.

AUG 13 2009

COPY

						CAD FILENAME/LAYERS R26069BA_TM26069C01/00A		
						PANDUIT CORP TINLEY PARK, ILLINOIS		
						BT75SDT * CUSTOMER DRAWING		
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .01 (XXX) ± .005 (.XX) ± .005 ANGLES ± .005		
						UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION		
						SCALE NONE		
						DRAWING NO. TM26069C01		
						DWG SIZE C		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUS	SUP
00	04-30-09	PWG		RELEASED	4377	--		