PD-93760C

International
IOR Rectifier

IRF7530

HEXFET® Power MOSFET

- Trench Technology
- Ultra Low On-Resistance
- Dual N-Channel MOSFET
- Very Small SOIC Package
- Low Profile (<1.1mm)
- Available in Tape & Reel



Top View

V_{DSS} = 20V

$R_{DS(on)}$ = 0.030Ω

Description

New trench HEXFET® power MOSFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The new Micro8™ package has half the footprint area of the standard SO-8. This makes the Micro8 an ideal device for applications where printed circuit board space is at a premium. The low profile (<1.1mm) of the Micro8 will allow it to fit easily into extremely thin application environments such as portable electronics and PCMCIA cards.


Micro8™

Absolute Maximum Ratings

	Parameter	Max.	Units
V_{DS}	Drain- Source Voltage	20	V
I_D @ T_A = 25°C	Continuous Drain Current, V_{GS} @ 4.5V	5.4	A
I_D @ T_A= 70°C	Continuous Drain Current, V_{GS} @ 4.5V	4.3	
I_{DM}	Pulsed Drain Current ①	40	
P_D @T_A = 25°C	Power Dissipation	1.3	W
P_D @T_A = 70°C	Power Dissipation	0.80	
	Linear Derating Factor	10	mW/°C
E_{AS}	Single Pulse Avalanche Energy④	33	mJ
V_{GS}	Gate-to-Source Voltage	± 12	V
T_J, T_{STG}	Junction and Storage Temperature Range	-55 to + 150	°C

Thermal Resistance

	Parameter	Max.	Units
$R_{\theta JA}$	Maximum Junction-to-Ambient③	100	°C/W

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	20	—	—	V	V_{GS} = 0V, I_D = 250uA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	0.01	—	V/°C	Reference to 25°C, I_D = 1mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	—	—	0.030	Ω	V_{GS} = 4.5V, I_D = 5.4A ②
		—	—	0.045		V_{GS} = 2.5V, I_D = 4.6A ②
$V_{GS(th)}$	Gate Threshold Voltage	0.60	—	1.2	V	V_{DS} = V_{GS}, I_D = 250µA
g_{fs}	Forward Transconductance	13	—	—	S	V_{DS} = 10V, I_D = 5.4A
I_{DSS}	Drain-to-Source Leakage Current	—	—	1.0	µA	V_{DS} = 16V, V_{GS} = 0V
		—	—	25		V_{DS} = 16V, V_{GS} = 0V, T_J = 70°C
I_{GSS}	Gate-to-Source Forward Leakage	—	—	100	nA	V_{GS} = 12V
	Gate-to-Source Reverse Leakage	—	—	-100		V_{GS} = -12V
Q_g	Total Gate Charge	—	18	26	nC	I_D = 5.4A
Q_{gs}	Gate-to-Source Charge	—	3.4	5.1		V_{DS} = 16V
Q_{gd}	Gate-to-Drain ("Miller") Charge	—	3.4	5.1		V_{GS} = 4.5V ②
$t_{d(on)}$	Turn-On Delay Time	—	8.5	—	ns	V_{DD} = 10V
t_r	Rise Time	—	11	—		I_D = 1.0A
$t_{d(off)}$	Turn-Off Delay Time	—	36	—		R_G = 6.0Ω
t_f	Fall Time	—	16	—		R_D = 10Ω ②
C_{iss}	Input Capacitance	—	1310	—	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	—	180	—		V_{DS} = 15V
C_{rss}	Reverse Transfer Capacitance	—	150	—		f = 1.0MHz

Source-Drain Ratings and Characteristics

	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	---	---	1.3	A	MOSFET symbol showing the integral reverse p-n junction diode.
I_{SM}	Pulsed Source Current (Body Diode) ①	---	---	40		
V_{SD}	Diode Forward Voltage	—	—	1.2	V	T_J = 25°C, I_S = 1.3A, V_{GS} = 0V ②
t_{rr}	Reverse Recovery Time	—	19	29	ns	T_J = 25°C, I_F = 1.3A
Q_{rr}	Reverse RecoveryCharge	—	13	20	nC	di/dt = 100A/µs ②



Notes:

① Repetitive rating; pulse width limited by max. junction temperature.

② Pulse width ≤ 400µs; duty cycle ≤ 2%.

③ When mounted on 1 inch square copper board, t<10 sec

④ Starting T_J = 25°C, L = 2.6mH
R_G = 25Ω, I_{AS} = 5.0A. (See Figure 10)



Fig 1. Typical Output Characteristics



Fig 2. Typical Output Characteristics



Fig 3. Typical Transfer Characteristics



Fig 4. Normalized On-Resistance Vs. Temperature



Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage



Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage



Fig 7. Typical Source-Drain Diode Forward Voltage



Fig 8. Maximum Safe Operating Area



Fig 9. Maximum Drain Current Vs. Case Temperature



Fig 10. Maximum Avalanche Energy Vs. Drain Current



Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



Fig 12. On-Resistance Vs. Gate Voltage



Fig 13. On-Resistance Vs. Drain Current

Micro8™ Package Outline

Dimensions are shown in millimeters (inches)





LEAD ASSIGNMENTS



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.036	.044	0.91	1.11
A1	.004	.008	0.10	0.20
B	.010	.014	0.25	0.36
C	.005	.007	0.13	0.18
D	.116	.120	2.95	3.05
e	.0256 BASIC		0.65 BASIC	
e1	.0128 BASIC		0.33 BASIC	
E	.116	.120	2.95	3.05
H	.188	.198	4.78	5.03
L	.016	.026	0.41	0.66
θ	0°	6°	0°	6°



RECOMMENDED FOOTPRINT



NOTES:

1 DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1982.
2 CONTROLLING DIMENSION : INCH.
3 DIMENSIONS DO NOT INCLUDE MOLD FLASH.

Micro8™ Part Marking Information

EXAMPLE: THIS IS AN IRF7501



DATE CODE EXAMPLES:
YWW = 9503 = 5C
YWW = 9532 = EF

WW = (1-26) IF PRECEDED BY LAST DIGIT OF CALENDAR YEAR

YEAR	Y	WORK WEEK	W
2001	1	01	A
2002	2	02	B
2003	3	03	C
1994	4	04	D
1995	5		
1996	6		
1997	7		
1998	8		
1999	9		
2000	0	24	X
		25	Y
		26	Z

WW = (27-52) IF PRECEDED BY A LETTER

YEAR	Y	WORK WEEK	W
2001	A	27	A
2002	B	28	B
2003	C	29	C
1994	D	30	D
1995	E		
1996	F		
1997	G		
1998	H		
1999	J		
2000	K	50	X
		51	Y
		52	Z

Micro8™ Tape & Reel Information

Dimensions are shown in millimeters (inches)



NOTES:
1. OUTLINE CONFORMS TO EIA-481 & EIA-541.
2. CONTROLLING DIMENSION : MILLIMETER.



NOTES :
1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

This product has been designed and qualified for the consumer market.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information.
Data and specifications subject to change without notice. 04/04