





(E)

STRIP MATERIAL NUMBER	FINISH
84590-0023	OVERALL NICKEL 80µ" MINIMUM



SELECT PLATING AREA
(CONTACT BEAM ONLY)



(E)

WIRE INSULATION O.D. RANGE $.075-.150$
 $1.91-3.81$

NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY .012/0.30 THICK.
HOOD MATERIAL: STAINLESS STEEL .008/0.20 THICK.
2. FINISH: SEE CHART.
3. STRIP TERMINALS ARE REELED AS SHOWN ABOVE,
3000 PARTS PER REEL.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR
ASSEMBLIES.
5. ALL DIMENSIONS ARE REFERENCE.
6. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

(E)

UPDATE NOTES & TABLE EC NO: WNA2008-0139 DRAWN: WLEUNG 2008/07/26 CHKD: RDEROSS 2008/04/21 APPR: RDEROSS 2008/04/24	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY	DATE	TITLE CONTACT SOCKET (HOODED), 14-18 AWG					
			4 PLACES ± ---	± ---	RSTONE	10/19/04						
			3 PLACES ± ---	± .010	CHECKED BY	DATE						
			2 PLACES ± 0.25	± .02	APLAZA	10/19/04						
			1 PLACE ± 0.5	± ---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED					
			ANGULAR ± 1 °		LROTHAUS	10/19/04						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.							
					SEE CHART		SD-84590-004		1 OF 1			
						SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					