



## FEATURES

- Intel® Atom™ N270 1.6GHz processor and Intel® 945GSE + ICH7-M chipset
- One 200-pin SO-DIMM supports DDR2 SDRAM up to 2GB
- Dual display (VGA / DVI), Dual Gigabit Ethernet and Dual serial ports
- Fan-less design is ideal for environment-critical application
- Optional DVD module
- Optional PCI/e x1 expansion slot for additional peripheral card
- Versatile mounting solutions such as Wall and Panel mount (Optional)
- Single DC 12V power input for easy system intergration

### SYSTEM

<b>CPU</b>	Intel® Atom™ N270 1.6GHz processor
<b>FSB</b>	533 MHz
<b>BIOS</b>	Award BIOS
<b>System Chipset</b>	Intel® 945GSE GMCH and ICH7-M
<b>System Memory</b>	One 200-pin SO-DIMM support DDR2 400/533 up to 2GB
<b>Storage</b>	- 1 x SATA 2.5" HDD - 1 x CF
<b>Watchdog Timer</b>	Programmable via S/W from 1sec. to 255min.
<b>H/W Status Monitor</b>	Temperature (CPU and System), Voltage, Case open function
<b>Expansion</b>	1 x Mini-PCI socket

### REAR PANEL

<b>Serial Port</b>	1 x RS232; 1 x RS232/422/485 selectable
<b>Display</b>	1 x VGA; 1 x DVI
<b>USB</b>	4 x USB 2.0
<b>KB/MS</b>	1 x K/B; 1 x Mouse
<b>Audio Interface</b>	Line-out and Mic-in
<b>Ethernet</b>	2 x Gigabit Ethernet


### Power Supply Unit

<b>Power Input</b>	DC 12V
<b>Adaptor</b>	AC 100~240V

### MECHANICAL & ENVIRONMENTAL

<b>Operation Temperature</b>	-5~45°C
<b>Storage Temperature</b>	-20~80°C
<b>Relative Humidity</b>	10~90% non-condensing
<b>Dimension (WxDxH)</b>	200x200x51 mm; 7.9"x7.9"x2" 200x200x83 mm; 7.9"x7.9"x3.3" (with optional module)
<b>Weight</b>	1.8 kg

## REAR I/O



### WEBS-3330-1602



### WEBS-3330-1603



## ORDERING GUIDE

- **WEBS-3330-1600**  
System with WADE-8070 (Atom™ N270 1.6GHz) + 2GB DDR2 + 120GB HDD
- **WEBS-3330-1602**  
System with WADE-8070 (Atom™ N270 1.6GHz) + 2GB DDR2 + 120GB HDD + DVD Module
- **WEBS-3330-1603**  
System with WADE-8070 (Atom™ N270 1.6GHz) + 2GB DDR2 + 120GB HDD + PCI/e x 1 expansion