

PROVA		Title	Calibration Procedures			Doc. No.	ADJ		Version	B	Date	Jul. 12, 1999
							-P2009	-01	Page	3/4		
Model		PROVA - 2009			Specification		In-House Production					
Step	Procedure	Range	Fixture	Input	VR	Location	Result					
13	Adjust	KW(600V)	25 Turn coil & Test leads	300V/1000A/ 50Hz PF=1	VR10		300.0KW (299.9KW ~ 300.1KW)					
14	Adjust	°C	Test leads	0°C	VR16		000.0°C (-000.1°C ~ 000.1°C)					
15	Adjust	°C	Test leads	300°C	VR17		300.0°C (299.9°C ~ 300.1°C)					
16	Adjust	°C	Test leads	900°C	VR18		900°C (899°C ~ 901°C)					
17												
18												
Revised date		Revised Doc.	Approver									
												Release

PROVA	Title	Calibration Procedure Annex	Doc. No.	ADJ	Version	B	Date	Jul. 12, 1999
				-P2009 -01	Page	4/4		

Graphic Illustration for NOTE 2



Figure I



Figure II

Revised date	Revised Doc.	Approver	Remark:				
			Release	Approve	Approve	Check	Design