

1.0 Preparation and company identity

Identification of the preparation

HP Laser Jet Cartridge C4096A

Company identification

**HEWLETT-PACKARD COMPANY
11311 Chinden Blvd.
Boise, ID 83714**

Telephone number

**Hewlett-Packard - General Information
208 323-2551****2.0 Composition/information on ingredients****This product is a toner preparation that is used in Hewlett-Packard LaserJet 2100M and 2100N printers.**

Ingredients

<u>Substance</u>	<u>CAS number</u>	<u>Percent (wt)</u>	<u>Symbol</u>	<u>R Phrase</u>
Styrene Acrylate Copolymer		40 - 50	-	-
Iron Oxide	(1317-61-9)	40 - 50	-	-

3.0 Hazards identification

Potential Health Effects

Ingestion effects: Ingestion is not applicable route of entry for intended use.
Inhalation effects: Minimal respiratory tract irritation may occur with exposure to large amount of toner dust.
Eye Effects: May cause eye irritation.
Skin effects: Unlikely to cause skin irritation.

Environmental hazards

No particular hazards known.

4.0	First-aid measures
-----	--------------------

After ingestion

Rinse mouth with water. Drink one to two glasses of water. If symptoms occur, consult a physician.

After inhalation

Move person to fresh air immediately. If symptoms occur, consult a physician.

After contact with eyes

Immediately flush with large amounts of clean, lukewarm water (low pressure) for at least 15 minutes. If symptoms occur, consult a physician.

After contact with skin

Wash affected areas thoroughly with soap and water. If symptoms occur, consult a physician.

5.0	Fire-fighting measures
-----	------------------------

Flash Point (method used):

No data available

Ignition Temperature:

No data available

Flammability:

Non-flammable solid (according to test methods of USA 16 CFR 1500.44 and 84/449/EEC (Annex V))

Flammable Limits:

No data available

Extinguishing Media:

CO₂, water, dry chemicals

Special Fire Fighting Procedures:

None

Unusual Fire & Explosion Hazards:

Toner material, like most organic material in powder form, is capable of creating a dust explosion.

6.0	Accidental release measures
-----	-----------------------------

Spill and Leakage Procedures

Wear personal protective equipment as described in Section 8. Avoid breathing dust. Minimize the release of particles. Vacuum or sweep the material into a bag or other sealed container. If a vacuum is used, the motor must be rated as dust tight. A conductive hose bonded to the machine should be used to reduce static buildup. Dispose of waste toner in accordance with local requirements.

Environmental precautions

Do not discharge into drains (See also section 13 Disposal Considerations).

7.0	Handling and storage
-----	----------------------

Advise on safe handling and protection against fire

Keep material out of reach of children. Avoid inhalation of dust and contact with eyes. Keep away from excessive heat, sparks, and open flames. Use with adequate ventilation.

Requirements for storage rooms and advice on storage compatibility

Keep material out of reach of children. Keep container closed and store at room temperature. Keep away from strong oxidizers.

8.0 Exposure controls / personal protection

Exposure Limits For Toner:	
USA OSHA (TWA)/PEL):	15 mg/m³ (Total Dust)
	5 mg/m³ (Respirable Fraction)
ACGIH (TWA/TLV):	10 mg/m³ (Inhalable Particulate)
	3 mg/m³ (Respirable Particulate)
DFG (MAK):	6 mg/m³ (Feinstaubkonzentration)
(Also refer to Section 2.)	
Respiratory Protection:	Not required under intended use.
Ventilation:	Good general ventilation should be sufficient under intended use.
Protective Gloves:	Not required under intended use.
Eye Protection:	Not required under intended use.
Other Protective Equipment:	Not required under intended use.

9.0 Physical and chemical properties

Boiling Point:	Not applicable
Melting Point:	100 - 150°C (Softening Point)
Vapor Pressure (mmHg.):	Not applicable
Vapor Density (Air=1):	Not applicable
Solubility in Water:	Negligible
Solubility in Organic Solvents:	Partially soluble in toluene and xylene.
Specific Gravity (H ₂ O=1):	1.4 - 1.8
Percent Volatile by Volume:	Not applicable
Evaporation Rate (Butyl Acetate=1):	Not applicable
pH:	Not applicable
Appearance and Odor:	Fine black powder, slight plastic odor.

10.0 Stability and reactivity

Stability :	Stable
Incompatibility:	Strong oxidizers
Hazardous Decomposition Products:	Combustion will produce carbon dioxide and, possibly toxic chemicals such as carbon monoxide.
Hazardous Polymerization:	Will not occur.

11.0 Toxicological information**Acute Toxicity:**

Inhalation: **LC 50: >5mg/L/4 hrs. (rats, data from similar toner).**
Ingestion: **LD₅₀: > 2000mg/kg (rats, data from ingredients of toner)**
Eye Contact: **Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC based on test data of rabbits (data from ingredients of toner).**
Skin Contact: **Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC based on test data of rabbits.**

Chronic Toxicity:**No data available.****Mutagenicity:****Negative (Ames Test: Salmonella typhimurium)****Carcinogenicity:****Not a known or suspected carcinogen according to any IARC Monograph, NTP, OSHA Regulations (USA), EU Directive, or Proposition 65 (California).****Reproductive Toxicity:****Not classified as toxic according to Annex 1 of EU Directive 67/548/EEC, California Prop. 65, or DFG.****Sensitization:****Not classified as a sensitizer according to Annex 1 of EU Directive 67/548/EEC and strong sensitizer list of FHSA.****Other:****Sub-Acute Toxicity (Rat)- 90 day inhalation test, Test sample: magnetic toner (mean volume diameter is 6.0µm). No Observable Effect Level (NOEL): 16 mg/m³.****12.0 Ecological information****No data available for ecological and wastewater treatment (sewage) systems.****13.0 Disposal considerations**

Product / unused product / contaminated packaging (for Germany only)

Recommendation: consultation with the disposal agency and the relevant authorities; cleansing agent is water.**14.0 Transportation information****International Transport Information:**

UN No.: **None**
UN Shipping Name: **None**
Hazards Class: **None**
Packing Group: **None**
Special Precautions: **None**

15.0 Regulatory information

Chemicals Required to Report Under Sara Title III Section 313 (USA):

None

Chemicals Required to Report Under California Proposition 65 (USA):

None

Label Information According to the Directives 88/379/EEC and 67/548/EEC (EU):

Symbol and Indications:

Not required.

R Phrases:

Not required.

S Phrases:

Not required.

Dangerous Components (CAS No.) wt%:

None

Other:

None

Special provisions in relation to protection of man or the environment:

(EEC) 2455/92:

Not regulated.

76/769/EEC:

Not regulated.

(EC)3093/94

Not regulated.

Other:

None

USA Information

Signal Word

Not required.

Hazard Warning

Not required.

Safety Advice

Not required.

Hazardous Components

None

16.0 Other information

This information is based on our present state of knowledge. It should not therefore be construed as guaranteeing specific properties of the products as described or their suitability for a particular application.

For general information, contact Hewlett-Packard at 208 323-2551.