



Main

Range of product	TeSys D
Product or component type	Contactor coil
Device short name	LXD1
Control circuit type	AC 50/60 Hz
Control circuit voltage	480 V AC 50/60 Hz
Average resistance	2398 Ohm at 20 °C
Inductance of closed circuit	87 H
Product compatibility	LC1D09...D38 LC1DT20...DT40
Operating time	12...22 ms closing 4...19 ms opening
Motor power HP (according to UL / CSA)	15 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.6 Uc at 60 °C drop-out 50/60 Hz 0.8...1.1 Uc at 60 °C operational 50 Hz 0.85...1.1 Uc at 60 °C operational 60 Hz
Inrush power in VA	70 VA at 20 °C (cos φ 0.75) 60 Hz 70 VA at 20 °C (cos φ 0.75) 50 Hz
Hold-in power consumption in VA	7.5 VA at 20 °C (cos φ 0.3) 60 Hz 7 VA at 20 °C (cos φ 0.3) 50 Hz
Heat dissipation	2...3 W at 50/60 Hz

Environment

Ambient air temperature for operation	-5...60 °C
Product weight	0.07 kg