


**Item # 782XBXC-6D, 782 Ice Cube Relays / DPDT 15 Amp Rating**



[Specifications](#) · [Coil Characteristics](#) · [Performance Characteristics](#) · [Environment](#) · [Product Certifications](#)

**Specifications**

Check Inventory	<a href="#">Check Distributor Inventory</a>
Status	NCNR
Legacy Part No.	W78RCSX-6
Terminal Style	Plug-in
Contact Configuration	DPDT
Thermal (Carrying) Current	15 A
Coil Resistance (Ohms)	40 Ohm
Load Type	Standard
Contact Materials	Silver Alloy
Maximum Switching Voltage (V)	300 V
Switching Current at Voltage (AC, Resistive)	10 A at 277 V 50/60 Hz (CSA) 12 A at 277 V 50/60 Hz 15 A at 120 V 50/60 Hz
Switching Current at Voltage (DC, Resistive)	12 A at 28 V
Switching Current at Voltage (HP)	1 at 250 VAC hp 1/2 at 120 VAC hp
Pilot Duty	B300
Minimum Switching Requirement	100 mA at 5 VDC (0.5 W)
Cover Options	Plain Cover
Features	Mechanical flag indicator

**Coil Characteristics**

Coil Voltage	6 VDC
Operating Range - % of Nominal (AC)	85 to 110 %
Operating Range - % of Nominal (DC)	80 to 110 %
Average Consumption (AC / VA)	1.20 VA

Average Consumption (DC / W)	0.90 W
Drop-out Voltage Threshold (AC)	15 %
Drop-out Voltage Threshold (DC)	10 %

---

#### Performance Characteristics

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
Mechanical Life, Unpowered	10000000
Operating Time (Response Time)	20 ms
Dielectric Strength - Between Coil and Contact (AC)	2500 V(rms)
Dielectric Strength - Between Poles (AC)	1500 V(rms)

---

#### Environment

Ambient Air Temperature around the Device - Storage	-40 to +85 C
Ambient Air Temperature around the Device - Operation	-40 to +55 C
Vibration Resistance - Operational	3 g-n at 10-55 Hz
Shock Resistance	10 g-n
Degree of Protection	IP 40

---

#### Product Certifications

Agency Approvals	CSA (LR40787) UL (E43641) CE RoHS
------------------	--