



©1969 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PENDING.

UNPUBLISHED COPY NOT TO BE REPRODUCED NOR PUBLICLY USED WITHOUT WRITTEN PERMISSION OF AMP INCORPORATED.



NOTE:
1. NICKEL PL (Q&N-290).0002 MIN EXT THK

REVISIONS			
ZONE	TR	DESCRIPTION	DATE
0		NPS 69-0023 (REV 1)	8/2/86 RJW

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ±.008 ANGLES ± 5		CONTRACT NO. — 4 —		DATE 2-17-69	
MATERIAL COPPER (Q&C-576)		CHK BY <i>Wm. Cunningham</i>		DATE 2-18-69	
HEAT TREAT ANNEALED		APPROD <i>Wm. Cunningham</i>		DATE 2-20-69	
FINISH NOTE 1		OSGN APPD		SCALE NTS	
LOC PRINT DIST G 14 0		OTHER APPD		WT CALC ACTUAL	
AMP INFO		AMP INCORPORATED HARRISBURG, PENNSYLVANIA		WIRE TERMINAL WIRE SIZE: 16-14	
G 14 0		B 100779		52195	
				1 OF 1	