

Datasheet

2 Pin LED Cluster Lamp, White, 60 mA, 230 V ac

Stock Number: 720-3782



- **Direct drop-in replacement**
- **No need to remove the magnetic ballast**
- **50,000 hours** life expectancy
- **Super-bright** - > 64 lumens per watt
- Consume only **7W** and **14W**
- **2-pin** or **4-pin**

Schools	Wash Rooms
Hospitals	Hotels
Car Parks	Bars / Pubs
Universities / Colleges	Clubs
Sports Centres	Warehouses
Stairways and Corridors	Cold Rooms



ENGLISH

Lamp

Colour Temperature

Pure White (5000°K)

Warm White (3250°K)

Lamp Life

up to 50,000 hours

Built in redundancy against LED failure

Environmental

Operating Temperature

-20°C...+30°C

Storage Temperature

-40°C...+65°C

Relative Humidity

0% to 90% Non-condensing

Materials

Case

Flame-retardant ABS V0 rated

Lens

Polycarbonate V2 rated

Voltage & Connection

230 V ac +/- 5% (see label), 50 Hz

Internal fuse protection

200mA (not user replaceable)

Remove the starter and any power factor capacitor installed in the fitting. **Any modification required to the fitting should be undertaken only by a qualified electrician.** The owner/installer must satisfy themselves that the lamp is suitable for use and may be used safely in a given fitting.