

## Housing - HC-B 32-TFQ-80/O1PG29S - 1675094


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for double locking latch, height 80 mm, without screw connection, 1x Pg29, lateral cable entry



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 149857
Weight per Piece (excluding packing)	438.09 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	80 mm
Width	79 mm
Length	94 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B32, DD144, M
Type	B32
Housing type	Sleeve housing
Locking type	For double locking latch
No. of cable outlets	1
Cable exit	Lateral
Screw connection	none
Type of the screw connection	1x Pg29
Housing material	Aluminum die-cast

# Housing - HC-B 32-TFQ-80/O1PG29S - 1675094

## Technical data

### General

Housing surface material	Powder-coated, gray
--------------------------	---------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

Approval details

# Housing - HC-B 32-TFQ-80/O1PG29S - 1675094

## Approvals

EAC

## Drawings

Dimensional drawing

