


## Data sheet

Commercial Art.No.: 57.403.6955.1

Multi-tier terminal WKN2,5E / U VB SW/V0

Duo Feed-through terminal with Screw connection for mounting on TS 35/ TS 32, nominal cross section: 2.5 mm<sup>2</sup>, Width: 5 mm, Color: black



Commercial Art.No.	57.403.6955.1
EAN	4015573599918
Order Unit	100

Certificates / Approvals



## Technical data

### General

Nominal cross section	2.5 mm <sup>2</sup>
Colour	Black
Number of levels	2
Number of clamp positions per level	2
Width/grid dimension	5 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Explosion-tested version "Ex e"	No
Mounting method	DIN rail (top hat rail)/G-rail
Terminal blocks for electrical installations	No

### Technical data

Rated current	24 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Closing plate required	Yes
Type of insulation material	Thermoplastic
Length	65.8 mm

### Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	0.2 mm <sup>2</sup>
Maximum cross section solid	4 mm <sup>2</sup>
Minimum cross section fine stranded	0.14 mm <sup>2</sup>
Maximum cross section fine stranded	2.5 mm <sup>2</sup>
Wire strip length	8 mm

Torque conductor mounting	0.4 Nm
---------------------------	--------

**Technical Data UL/CSA**

Cross section UL	22-12 AWG
Voltage UL	600 V
Current factory wiring	25 A
Current field wiring	20 A
Cross section CSA	24-12 AWG
Voltage CSA	600 V
Current CSA	25 A

**Classification**

ECLASS 8.1	27141120
ETIM 7.0	EC000897
ETIM 6.0	EC000897
ETIM 5.0	EC000897
ETIM 4.0	EC000897
ETIM 3.0	EC000897

**Accessories**

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------

**Fits with**

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------