

# BJDL6-3

## General Information

<b>Extended Product Type:</b>	BJDL6-3
<b>Product ID:</b>	1SNA291129R2500
<b>EAN:</b>	3472592911298
<b>Catalog Description:</b>	BJDL6-3 Jumper Bars
<b>Long Description:</b>	BJDL6-3 - Jumper Bars - 3 poles - Orange - 6mm Spacing



## Categories

Products » Low Voltage Products and Systems » Connection Devices »  
Terminal Blocks Accessories » Jumper Bars

## Ordering

<b>EAN:</b>	3472592911298
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	39269097

## Dimensions

<b>Product Net Weight:</b>	0.001 kg
----------------------------	----------

## Container Information

<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	168 mm
<b>Package Level 1 Length:</b>	250 mm
<b>Package Level 1 Gross Weight:</b>	0.02 kg
<b>Package Level 1 EAN:</b>	3472592911298
<b>Package Level 2 Units:</b>	6000 piece
<b>Product Packing Type:</b>	Bag

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Additional Information

<b>Color:</b>	Orange
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Function:</b>	Jumper Bars
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Poles:</b>	3
<b>Product Main Type:</b>	BJDL
<b>Product Name:</b>	Jumper Bar

<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 32 A
<b>RoHS Date:</b>	18 08 2005
<b>Spacing:</b>	6 mm

---

### **Certificates and Declarations (Document Number)**

---

<b>GOST Certificate:</b>	1SND161005A1103
<b>RoHS Information:</b>	1SND230492F0201

---

### **Classifications**

---

<b>ETIM 4.0:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5.0:</b>	EC000489 - Cross-connector for terminal block
<b>Object Classification Code:</b>	X

---