

# GPN9




RS Pt No: 472 1284

GPN9

The Printed Motor Works GPN9 is a totally enclosed dc motor in an ultra slim pancake profile. This pancake motor can provide a cost effective servo capability either direct drive or combined with a timing pulley/gearbox.

## Features & Benefits

- Ultra slim profile
- Minimum torque ripple
- Very low inertia
- High peak torques
- Zero cogging
- Ultra slow/creep capability
- Low inductance
- EMC compatible



NOTE: The above voltages are examples, not a predefined maximum or minimum. Due to ongoing product improvements data is subject to change without notice.

**Applications:** Servo mechanisms, motion control, industrial robots, CNC machining, printing machinery, logistics solutions, medical mobility, medical scanners, flight simulators, marine autopilots and high ambient temperature ventilation.

**Markets:** Industrial automation, automotive, medical, life sciences, aerospace, printing, logistics, instrumentation, test and measurement, oil & gas and offshore marine.

**Design Modifications**

- Encoders
- Timing pulleys
- Long leads
- Tri-rated cable
- Open/kit option
- Customised shafts
- EMC suppression
- Connectors
- Rated for operation in 150°C ambient
- Mounting customisation

Performance Specifications	Symbol	Units	GPN9
Peak Torque	Tp	N-cm (oz-in)	300 (424.8)
Rated Speed	N	RPM	3000
Rated Continuous Torque @ 25°C	T <sub>25</sub>	N-cm (oz-in)	33 (46.73)
Rated Power Output	P	Watts	94
Maximum Recommended Speed	Nmax	RPM	6000
Continuous Stall Torque	Ts	N-cm (oz-in)	20.27 (28.7)
Cogging Torque	Tc	N-cm (oz-in)	0 (0)
<b>Electrical Specifications</b>			
Rated Terminal Voltage	E	Volts	22.5
Rated Continuous Current	I	Amps	6.85
Peak Current	Ip	Amps	63.2
Continuous Stall Current	Is	Amps	6
<b>Winding Specifications</b>			
Terminal Resistance ± 10%	Rm	Ohms	1.1
Armature Resistance ± 10%	Ra	Ohms	0.719
Back EMF Constant ± 5%	Ke	V/kRPM	5
Torque Constant ± 5%	Kt	N-cm/Amp (oz-in/Amp)	4.77 (6.76)
Viscous Damping Constant	Kd	N-cm/KRPM (oz-in/KRPM)	0.5 (0.71)
Armature Inductance	L	µH	<0.03
Temperature Coefficient of KE	C	%/°C Rise	-0.19
Number of Commutation Bars	Z		117
<b>Mechanical Specifications</b>			
Moment of Inertia	Jm	Kg-cm <sup>2</sup> (oz-in-sec <sup>2</sup> )	0.39 (0.0055)
Average Friction Torque	Tf	N-cm (oz-in)	1.2 (1.7)
Weight	W	kg (Ibs)	0.6 (1.32)
Diameter	D	mm (In)	120 (4.724)
Length	LG	mm (In)	26 (1.024)
Permitted Radial Load		Kg (Ibs)	2 (4.41)
Permitted Axial Load		Kg (Ibs)	1 (2.21)
<b>Figure of Merit</b>			
Mechanical Time Constant	Tm	ms	18.7
Electrical Time Constant	Te	ms	<0.09
<b>Thermal Specifications</b>			
Thermal Resistance at Rated Speed	RAAR	°C/Watt	2
Thermal Resistance at Stall	RAAS	°C/Watt	2.52