

## Base strip - CIOC 3-1-FV-A - 1701551

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 3 A, Rated voltage (III/2): 32 V, Number of positions: 3, Pitch: 2 mm, Color: black, Contact surface: Gold, Mounting: Soldering


The illustration shows the 4-pos. version

### Why buy this product

- 3 and 4-pos. miniature headers for CIOC ...-M plugs
- Gold-plated contact system
- Enables the space-saving design of I/O modules and signal distributors



### Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 543514
Weight per Piece (excluding packing)	2.28 g
Custom tariff number	85366990
Country of origin	Japan

### Technical data

#### Dimensions

Pitch	2 mm
Dimension a	4 mm
Pin spacing	2.00 mm

#### General

Range of articles	CIOC-FV
Rated voltage (III/2)	32 V
Connection in acc. with standard	EN-VDE
Nominal current $I_N$	3 A
Maximum load current	3 A
Insulating material	PA

# Base strip - CIOC 3-1-FV-A - 1701551

## Technical data

### General

Inflammability class according to UL 94	V0
Color	black
Number of positions	3

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

# Base strip - CIOC 3-1-FV-A - 1701551

## Approvals

UL Recognized	
Nominal current $I_N$	3 A
Nominal voltage $U_N$	32 V


cUL Recognized	
Nominal current $I_N$	3 A
Nominal voltage $U_N$	32 V

EAC

cULus Recognized	
------------------	--

## Drawings

Drilling diagram



Dimensioned drawing

