

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Ethernet switch, 4 TP RJ45 ports, 3 FO ports, 100 Mbps full duplex in ST-D format, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), auto crossing function

Your advantages

- ✓ Auto negotiation and autocrossing detection simplifies installation and setup
- ✓ Relay contact for alarm processing of voltage states
- ✓ Security options with cable locking
- ✓ Local diagnostic indicators with LEDs
- ✓ RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 044097 |
| GTIN | 4046356044097 |
| Weight per Piece (excluding packing) | 140.000 g |
| Custom tariff number | 85176200 |
| Country of origin | Taiwan |

Technical data

Note

| | |
|-------------------------|---|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---|

Dimensions

| | |
|--------|----------|
| Width | 135 mm |
| Height | 115.3 mm |
| Depth | 30 mm |

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP20 |
|----------------------|------|

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Technical data

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | 0 °C ... 55 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 86 kPa ... 108 kPa (up to 1500 m above sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (up to 3500 m above sea level) |

Interfaces

| | |
|-------------------------------|---|
| Interface | Ethernet (RJ45) |
| No. of ports | 4 (RJ45 ports) |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission speed | 10/100 Mbps |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| Interface | Fiber optic interface |
| No. of ports | 3 (ST multi-mode) |
| Transmission physics | multi-mode fiberglass |
| Transmission speed | 100 Mbps (full duplex) |
| Transmission length | 6400 m (fiberglass with F-G 50/125 0.7 dB/km F1200) |
| Wavelength | 1300 nm |
| Interface | Potential-free signaling contact |
| Connection method | Plug-in/screw connection via COMBICON |

Function

| | |
|----------------------------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
| Additional functions | Autonegotiation |
| Status and diagnostic indicators | LEDs: U_{S1} , U_{S2} (redundant voltage supply), link and activity per port |

Network expansion parameters

| | |
|---|--|
| Cascading depth | Network, linear, and star structure: any |
| Maximum conductor length (twisted pair) | 100 m |

Supply voltage

| | |
|-----------------------------|--|
| Supply voltage | 24 V DC (redundant) |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Supply voltage range | 18.5 V DC ... 30.2 V DC |
| Typical current consumption | 240 mA (at $U_S = 24$ V DC) |

General

| | |
|---------------|--------------|
| Mounting type | DIN rail |
| Type AX | Block design |
| Net weight | 140 g |

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Technical data

General

| | |
|------------------|----------|
| Housing material | Aluminum |
|------------------|----------|

Standards and Regulations

| | |
|----------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Noise emission | EN 61000-6-4 |
| Noise immunity | EN 61000-6-2:2005 |
| Vibration (storage/transport) | 5g, 150 Hz, in acc. with IEC 60068-2-6 |
| Connection in acc. with standard | CUL |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |

Environmental Product Compliance

| | |
|------------|---|
| | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 10; |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 19170402 |
| eCl@ss 4.0 | 27250501 |
| eCl@ss 4.1 | 27250501 |
| eCl@ss 5.0 | 27250501 |
| eCl@ss 5.1 | 19030100 |
| eCl@ss 6.0 | 19170100 |
| eCl@ss 7.0 | 19170106 |
| eCl@ss 8.0 | 19170106 |
| eCl@ss 9.0 | 19170106 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000734 |
| ETIM 3.0 | EC000734 |
| ETIM 4.0 | EC000734 |
| ETIM 5.0 | EC000734 |
| ETIM 6.0 | EC000734 |
| ETIM 7.0 | EC000734 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11 | 43172015 |
| UNSPSC 12.01 | 43201410 |
| UNSPSC 13.2 | 43222612 |

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

| | | | |
|-----------|--|---|---------------|
| UL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 140324 |
|-----------|--|---|---------------|

| | | | |
|------------|--|---|---------------|
| cUL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 140324 |
|------------|--|---|---------------|

| | | | |
|-----|--|--|---------------|
| EAC | | | EAC-Zulassung |
|-----|--|--|---------------|

| | | | |
|-----|--|--|--------------------------|
| EAC | | | RU *- DE.A*30.B.01735 |
|-----|--|--|--------------------------|

| | | | |
|--------------|--|--|--|
| cULus Listed | | | |
|--------------|--|--|--|

Accessories

Accessories

Drivers and interfaces

Software - FL SNMP OPC SERVER - 2832166



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Accessories

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250

Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276

Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221

Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289

Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292

Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580

Patch cable, CAT5, assembled, 5 m

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Accessories

Patch cable - FL CAT5 PATCH 7,5 - 2832616

Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629

Patch cable, CAT5, assembled, 10 m

Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.



RJ45 connector - FL PLUG RJ45 GN/2 - 2744571

RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.



Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Safety locking

Industrial Ethernet Switch - FL SWITCH SF 4TX/3FX ST - 2832603

Accessories

Port Guard Security Element - FL SEC PAC 4TX - 2832865

Layer1 security elements for four RJ45 network connections for use with patch boxes and panels



Universal tools

Assembly tool - FL CRIMPTOOL - 2744869

Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site



Patch box - FL PBX 8TX - 2832496



Patch box with eight RJ45 network connections

Patch box - FL PBX 6TX/4FX - 2832506



Patch box with six RJ45 and four FO network connections