



Price\* : 45.29 GBP



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D6
Control circuit type	AC 50 Hz
[Uc] control circuit voltage	415 V AC 50 Hz
Average resistance	463 Ohm at 20 °C
Inductance of closed circuit	26 H
Product compatibility	LC1D80 LC1D95
Mechanical durability	10 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.6 Uc at 55 °C drop-out 50/60 Hz 0.8...1.1 Uc at 55 °C operational 50 Hz 0.85...1.1 Uc at 55 °C operational 60 Hz
Inrush power in VA	200 VA at 20 °C (cos f 0.75) 50 Hz
Hold-in power consumption in VA	20 VA at 20 °C (cos f 0.3) 50 Hz
Heat dissipation	6...10 W at 50/60 Hz

## Environment

Ambient air temperature for operation	-5...60 °C
Product weight	0.28 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0847 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Available <a href="#">End of life manual</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------