

Residual Current Breakers with Overload Protection RCBo

DS203 M AC-C63/0,03

General Information

Extended Product Type:	DS203 M AC-C63/0,03
Product ID:	2CSR273001R1634
EAN:	8012542853404
Catalog Description:	DS203 M AC-C63/0,03 - RCBo

Long Description:

The RCBOs DS200 series has the function to protect against overload and short-circuit currents; protection against effects of sinusoidal alternating earth fault currents; protection against indirect contacts and additional protection against direct contacts.

Ordering

EAN:	8012542853404
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85363030

Dimensions

Product Net Width:	0.122 m
Product Net Height:	0.093 m
Product Net Depth:	0.069 m
Product Net Weight:	0.650 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.105 m
Package Level 1 Height:	0.08 m
Package Level 1 Length:	0.15 m
Package Level 1 Gross Weight:	0.71 kg
Package Level 1 EAN:	8012542853404
Package Level 2 Units:	1 piece
Package Level 2 Width:	0.15 m
Package Level 2 Height:	0.105 m
Package Level 2 Length:	0.08 m
Package Level 2 Gross Weight:	0.71 kg
Package Level 2 EAN:	8012542853411

Environmental

RoHS Status:

Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q4

Additional Information

IIT Publishing Status:	Level 0 - Information enabled
Number of Poles:	3

Number of Protected Poles:	3
Power Loss:	Per Pole 28.2 W
Product Main Type:	DS200
Product Name:	Residual Current Breaker with Overload Protection
Rated Current (I_n):	63 A
Rated Residual Current:	30 mA
Rated Short-Circuit Capacity (I_{cn}):	(230 / 400V AC) 10 kA
Standards:	IEC EN 61009
Tripping Characteristic:	C
Type of Residual Current:	AC type

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: [ITSCE129DS200](#)

Classifications

Object Classification Code: Q

