

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

G

14

P

F

ZONE

LTR

REVISIONS

DESCRIPTION

DATE

APPD

G EC 0720-0279-93

6-18-93

SSG BB

AMP
WIRE RANGE6 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

INSULATION

DIMPLED SURFACE

13.08
[.515]
MAX WASHER R

BODY

15.88
[.625]8.33±0.13
[.328±.005]
(FOR 5/16 STUD)36.75
[1.447] MAX44.75
[1.762] MAX1. TONGUE MATERIAL THK 1.14±0.08[.045±.003]
FOR 7.98[.314] MAX WIRE INS DIAAMP INCORPORATED
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

-

CIRCULAR MIL AREA:

10.5-16.8mm² [20,800-33,100]
STRANDEDTHIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.MS25036-121
CLASS 2

MILITARY P/N AND CLASS

QTY

LOOSE PC

PACKAGE TYPE

324048

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20[.008]
3 PLC DEC ± -
ANGLES ± -MATERIAL
COPPER PER ASTM B-152
NYLON (MIL-M-20693) TYPE 1
COLOR: BLUE

FINISH

TIN PLATE PER MIL-T-10727

DR 6-18-93
S.S. GOULDEN
CHK 6-18-93
R. HERSEY
APPD 6-18-93
B. BARE
APPD 6-18-93
M. ELLIS

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 6 AWG

SIZE

CAGE CODE

DRAWING NO

B

00779

C-324048

SCALE

NTS

SHEET

1 OF 1