






LOC		DIST		REVISIONS			
P	T	LTR	DESCRIPTION	DATE	DWN	APVD	
		S	REVISED PER ECO-12-015521	28SEP12	KH	MZ	



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

- 1
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2
- WILL ACCEPT FOURTEEN (14) MULTIMATE SOCKET CONTACTS.
- 3
- PRELIMINARY PART NUMBER.
- 4
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4	OBSOLETE	4-40 THREADED INSERTS	-	STANDARD	YES	A	206043-8
		Ø.150	-	SMALL PACK	NO	A	206043-6
		-	-	STANDARD	YES	B	206043-5
		Ø.150	-	STANDARD	YES	A	206043-4
		-	-	STANDARD	NO	B	206043-3
		Ø.150	206043-1	STANDARD	NO	A	206043-1
		DIM C	MOLDED PART NUMBER	PACKAGING	PERIPHERAL SEAL	SEE DETAIL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. LENKER CHK R. STONE	09/10/92 08/11/93	TE Connectivity		
	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± -	1 PLC ± -	PRODUCT SPEC		
		2 PLC ± 0.13 [.005]	3 PLC ± -	APPLICATION SPEC		
MATERIAL HOUSING: NYLON BLACK		FINISH -	WEIGHT -	SIZE A1		RESTRICTED TO -
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV S