







7 6 5 4 3 2 1



NOTE:
PHYSICAL

1. OUTER MOLD WITH BLACK PVC RESIN 887800042

ELECTRICAL PERFORMANCE:

- 2. DIELECTRONIC STRENGTH: 500V DC
- 3. INSULATION RESISTANCE: 100M OHMS
- 4. CONDUCTIVE RESISTOR: 2 OHMS

| MOLEX P/N | LENGTH (mm) | LENGTH (inch) | DESCRIPTION |
|------------|-------------|---------------|---|
| 68561-0017 | 1000+/-20 | 40.0+/-0.8 | S-ATA LATCHING STRAIGHT TO R/A CABLE. RED |
| 68561-0016 | 500+/-10 | 20.0+/-0.4 | S-ATA LATCHING STRAIGHT TO R/A CABLE. RED |

| ITEM | DESCRIPTION | L | QTY. |
|------|------------------------------------|-----|------|
| C | S-ATA STRAIGHT CONN. 674899002 | | 1 |
| B | 2PX26AWG S-ATA CABLE RED 887808052 | N/A | 1 |
| A | S-ATA R/A CONN. 674890002 | | 1 |

| | | | | | | | | | | | | |
|--|--|-------------------------------|--|------|----------------------------|---|------------------|---|------------------------|--|--|--|
| ENTER DESCRIPTION EC NO: DG2005-0009 DRWN: GXYANG CHKD: APPR: BOCHEN | 2004/08/11 2004/08/18 2004/08/18 | QUALITY SYMBOLS ▽=0 ◻=0 | GENERAL TOLERANCES (UNLESS SPECIFIED) | | DIMENSION STYLE MM ONLY | | SCALE --- | DESIGN UNITS METRIC | THIRD ANGLE PROJECTION | | | |
| | | | | mm | INCH | DRAWN BY GX YANG | DATE 04/08/10 | TITLE S-ATA STRAIGHT LATCHING TO R/A LATCHING SIGNAL CBL RED, 0.5M, 1.0M | | | | |
| | | | 4 PLACES | ±--- | ±--- | CHECKED BY TEDDY | DATE 04/08/10 | | | | | |
| | | | 3 PLACES | ±--- | ±--- | APPROVED BY BORON | DATE 04/08/10 | MOLEX INCORPORATED DOCUMENT NO. SD-68561-002 SHEET NO. 1 OF 1 | | | | |
| 2 PLACES | ±--- | ±--- | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | | | | | | | | |
| 1 PLACE | ±--- | ±--- | ANGULAR ±---° | | SIZE A/4 | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | |

6 5 4 3 2 1