



#### MC150M




M14x1 也可以提供特殊定制  
配件、装配、安装见 35~39 页

#### PP150




尼龙冲击头  
W<sub>3</sub> max = 14 Nm

#### RF14




矩形法兰

#### MB14




固定支架

#### MC225M




配件、装配、安装见 36~39 页

#### PP225




尼龙冲击头  
W<sub>3</sub> max = 33 Nm

#### RF20




矩形法兰

#### MB20




固定支架

#### MC600M




M27x3 也可以提供特殊定制  
配件、装配、安装见 36~39 页

#### PP600




尼龙冲击头  
W<sub>3</sub> max = 68 Nm

#### RF25



矩形法兰

#### MB25



固定支架

#### 产品规格表

型号 产品编号	最大吸收能量		有效重量 me 自补偿式		最小回弹力 N	最大回弹力 N	活塞杆复位 时间 s	1 最大偏角 °	重量 kg
	W <sub>3</sub> Nm/Cycle	W <sub>4</sub> Nm/h	me min. kg	me. max. kg					
MC150M	20	34 000	0.9	10	3	8	0.4	4	0.06
MC150MH	20	34 000	8.6	86	3	8	0.4	4	0.06
MC150MH2	20	34 000	70	200	3	8	0.4	4	0.06
MC150MH3	20	34 000	181	408	3	8	1	4	0.06
MC225M	41	45 000	2.3	25	4	9	0.3	4	0.15
MC225MH	41	45 000	23	230	4	9	0.3	4	0.15
MC225MH2	41	45 000	180	910	4	9	0.3	4	0.15
MC225MH3	41	45 000	816	1 814	4	9	0.3	4	0.15
MC600M	136	68 000	9	136	5	10	0.6	2	0.26
MC600MH	136	68 000	113	1 130	5	10	0.6	2	0.26
MC600MH2	136	68 000	400	2 300	5	10	0.6	2	0.26
MC600MH3	136	68 000	2 177	4 536	5	10	0.6	2	0.26

1 如果应用场合偏角过高，请考虑使用偏角转接器 (BV)。(35 页~38 页)