

TT-SLKK5/110AC

Order No.: 2794987

The illustration shows version TT-SLKK5/ 12 DC

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794987>

Modular terminal block with varistor as surge voltage protection between clamping connector and DIN rail, separate ground connection, nominal voltage: 110 V AC, mounting on NS 35/7,5, terminal width: 6.2 mm, terminal height: 69 mm

Commercial data

EAN	4017918073053
Pack	50 Pcs.
Customs tariff	85363030
Weight/Piece	0.02171 KG
Catalog page information	Page 69 (TT-2005)

Product notes

WEEE/RoHS-compliant since:
06/28/2006

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing material	PA
Inflammability class acc. to UL 94	V2
Color	black

Total surge current (8/20) μ s	6.5 kA
Ambient temperature (operation)	-40 °C ... 85 °C
Mounting type	DIN rail 35 mm
Design	Single-level terminal block – separate PE connection
Number of positions	1
Degree of protection	IP20
Direction of action	Line-Earth Ground
Width	6.20 mm
Height	69.50 mm
Length	66.50 mm

Protective circuit

IEC category	C1
	C2
	C3
VDE requirement class	C1
	C2
	C3
Nominal voltage U_N	110 V AC
Max. operating voltage U_{max}	130 V AC
Arrester rated voltage U_C (Core-Earth)	130 V AC
Nominal current I_N	32 A (50°C)
Discharge current to PE at U_C	$\leq 100 \mu$ A
Nominal discharge surge current I_n (8/20) μ s (Core-Earth)	2 kA
Total surge current (8/20) μ s	6.5 kA
Max. discharge surge current I_{max} (8/20) μ s maximum (Core-Earth)	6.5 kA
Nominal power pulse current I_{an} (10/1000) μ s (Core-Earth)	75 A
Output voltage limitation at 1 kV/ μ s (Core-Earth) spike	≤ 310 V
Output voltage limitation at 1 kV/ μ s (Core-Earth) static	≤ 310 V
Residual voltage at I_n , (conductor-ground)	≤ 500 V
Response time t_A (Core-Earth)	≤ 25 ns
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ohm system	Typ. 1.5 MHz

General

Type of connection	Screw connection
Connection type IN	Screw terminal blocks
Connection type OUT	Screw terminal blocks
Screw thread	M 3
Tightening torque, min	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Connection, protective circuit

Standards/regulations	IEC 61643-21
-----------------------	--------------

Certificates / Approvals

Approval logo



CSA

Nominal voltage U _N	110 V
Nominal current I _N	34 A
AWG/kcmil	28-12

CUL

Nominal voltage U _N	110 V
Nominal current I _N	30 A
AWG/kcmil	26-12

UL

Nominal voltage U _N	110 V
Nominal current I _N	30 A
AWG/kcmil	26-10

Certification	CSA, CUL, GOST, UL
---------------	--------------------

Accessories

Item	Designation	Description
------	-------------	-------------

Assembly

2770228	D-UKK 3/5 BK	Cover for setting the end of a TERMITRAB TT-SLKK5... row of terminal blocks, color: black
2770833	DP-UKK 3/5 BK	Spacer plate, compensates for level offset if standard terminal blocks are to be fitted adjacently, 2.5 mm thick

Marking

1051993	B-STIFT	Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm
1051016	ZB 6,LGS:FORTL.ZAHLEN	Zack strip, 10-section, printed horizontally: with the numbers, 1-10, 11-20 etc. up to 991-1000, color: white
1051414	ZB 6,LGS:L1-N,PE	Zack strip, printed horizontally, strips with 10 labels, L1, L2, L3, N, PE, L1, L2, L3, N, PE, color: white
1051430	ZB 6,LGS:U-N	Zack strip, printed horizontally: 10-section, U, V, W, N, GND, U, V, W, N, GND, color: white
1050499	ZB 6:SO/CMS	Zack strip, 10-section, divisible, special printing, marking according to customer requirements
1051003	ZB 6:UNBEDRUCKT	Zack strip, unprinted, strips with 10 labels for individual labeling with M-PEN or CMS system, for terminal block width: 6.2 mm, color: white
0808749	ZBF 6,LGS:FORTL.ZAHLEN	Zack strip, flat, printed horizontally: 10-section, with the numbers, 1-10, 11-20 etc. up to 991-1000, color: White
0808736	ZBF 6/WH-100:UNBEDRUCKT	Zack strip, flat, unprinted: 10-section, for individual labeling with M-PEN or ZBF-T, large batch, sufficient for labeling 1000 terminal blocks, color: white
0808710	ZBF 6:UNBEDRUCKT	Zack strip, flat, unprinted: 10-section, for individual labeling with M-PEN or ZBF-T, sufficient for 100 terminal blocks, color: white

Additional products

Item	Designation	Description
------	-------------	-------------

Assembly

2770228	D-UKK 3/5 BK	Cover for setting the end of a TERMITRAB TT-SLKK5... row of terminal blocks, color: black
2770833	DP-UKK 3/5 BK	Spacer plate, compensates for level offset if standard terminal blocks are to be fitted adjacently, 2.5 mm thick
2839295	SSA 3-6	shield fast connections for conductor cross sections 3 - 6 mm. Potential connection cable: 200 mm, black

2839512	SSA 5-10	Shield fast connection for conductor cross sections 5 - 10 mm. Potential connection cable: 200 mm, black
---------	----------	---

Drawings

Circuit diagram

