


Terminal blocks spring connection

Standard



End stop		th. 9 mm	BADL	V0	0399 903.02
End stop		th. 9,1 mm	BAM	V2	0103 002.26
End stop		th. 9,1 mm	BAM V0	V0	0199 306.03
Rail		35 x 7,5 x 1	PR3.Z2		0174 300.17
Rail		35 x 15 x 2,3	PR4		0168 500.12
Rail		35 x 15 x 1,5	PR5		0168 700.22

Other end stops, rails and accessories : see section on accessories.


Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

One wire per spring.

Terminal block body material is UL 94 V0.

Accessories



1	End section	grey	FED5.2L	V0	th. 2,5 mm	0291 061.24
		orange	FED5.2L	V0	th. 2,5 mm	0291 062.25
2	Separator	orange	SCD5.2L	V0	th. 2,5 mm	0291 352.04
3	Test plug	black	FC2	V2	DIA. 2 mm	0007 865.26
4	Jumper bar	orange	BJDL6.2	V0	2 poles	0291 128.24
	IP 20 - 32 A		BJDL6.3	V0	3 poles	0291 129.25
			BJDL6.4	V0	4 poles	0291 194.17
			BJDL6.5	V0	5 poles	0291 195.10
5	Jumper bar	orange	BJDPL56	(1)		0291 150.06
	For blocks of different spacing		BJDPL68	(1)		0291 170.02
	- Spacing 5 and 6 mm IP 20 - 24 A		BJDPL610	(1)		0291 482.10
	- Spacing 5 and 8 mm IP 20 - 24 A					
	- Spacing 5 and 10 mm IP 20 - 24 A					
	- Spacing 6 and 8 mm IP 20 - 32 A					
	- Spacing 6 and 10 mm IP 20 - 32 A					
	- Spacing 8 and 10 mm IP 20 - 41 A					


R



R See section on markers marking method

D 4/6.2L

Spacing 6 mm +0,05 .238"



2 springs.



Color	Type	Part number
Grey	D 4/6.2L	0290 061.07
Orange	D 4/6.2L	0290 062.00
Blue	D 4/6.N.2L	0290 063.01

Characteristics

Wire size	IEC		UL/CSA
	NFC	DIN	
Solid wire	0,2-6 mm ²		24-10 AWG
Stranded wire	0,2-4 mm ²		24-10 AWG
With isolated ferrule	0,5-4 mm ²		


Voltage		
Rated	800 V	600 V
Pulse	8 kV	
Pollution degree	3	

Current		
Rated	32 A	25 A

Wire size			
Rated / Gauge	4 mm ² / A4		10 AWG
Wire strip. length	Recomm. torque	Protection	
11 mm	4 mm	IP 20	
.43"	.16"	NEMA 1	

D 4/6.3L

Spacing 6 mm +0,05 .238"



3 springs.



Color	Type	Part number
Grey	D4/6.3L	0290 405.06
Orange	D 4/6.3L	0290 406.07
Blue	D 4/6.N.3L	0290 407.00

Characteristics

Wire size	IEC		UL/CSA
	NFC	DIN	
Solid wire	0,2 -6 mm ²		24-10 AWG
Stranded wire	0,2-4 mm ²		24-10 AWG
With isolated ferrule	0,5-4 mm ²		

Voltage		
Rated	800 V	600 V
Pulse	8 kV	
Pollution degree	3	

Current		
Rated	32 A	25 A

Wire size			
Rated/gauge	4 mm ² / A4		10 AWG
Wire strip. length	Recomm. torque	Protection	
11 mm	4 mm	IP 20	
.43"	.16"	NEMA 1	

Type	Part number	
FED5.2L V0	th. 2,5 mm	0291 061.24
FED5.2L V0	th. 2,5 mm	0291 062.25
SCD5.2L V0	th. 2,5 mm	0291 352.04
FC2 V2	DIA. 2 mm	0007 865.26
BJDL6.2 V0	2 poles	0291 128.24
BJDL6.3 V0	3 poles	0291 129.25
BJDL6.4 V0	4 poles	0291 194.17
BJDL6.5 V0	5 poles	0291 195.10
BJDPL56 (1)		0291 150.06
BJDPL68 (1)		0291 170.02
BJDPL610 (1)		0291 482.10

Type	Part number	
FED6.3L V0	th. 2,5 mm	0291 694.24
FED6.3L V0	th. 2,5 mm	0291 695.25
FC2 V2	DIA. 2 mm	0007 865.26
BJDL6.2 V0	2 poles	0291 128.24
BJDL6.3 V0	3 poles	0291 129.25
BJDL6.4 V0	4 poles	0291 194.17
BJDL6.5 V0	5 poles	0291 195.10
BJDPL56 (1)		0291 150.06
BJDPL68 (1)		0291 170.02
BJDPL610 (1)		0291 482.10

On top : RC 610 (6) or RPC (20)
On sides : RC 65 (5)

(1) End section must be inserted between 2 interconnected blocks.

On top : RC 610 (6) or RPC (20)
On sides : RC 65 (5)