

Micro Material

E-Denstone M Peach


EnvisionTEC's E-Denstone M Peach Material was developed for dental model manufacturing. The peach color provides an attractive choice for modeling that is similar in look and feel to common die stones used in labs. It can be used with traditional dental manufacturing methods or as a CAD based model solution. This is the only material that allows you to easily die trim, margin mark with a red pencil and hand wax to the die without concerns for layer lines. Die paint sticks to the dies just like plaster and won't peel off. The material looks and feels like traditional gypsum models, which sets it above the other resin-based models currently on the market. The low viscosity formula combined with high accuracy printers helps to produce superior results with no loss of anatomy detail. E-Denstone M Peach is also tough enough for a dental technician to repeatedly remove and replace the die, check occlusion and move through excursions without any loss of fit or causing excessive wear on the contact surfaces. The cleanup does not use messy oils or heat that can cause distortion and takes only 3 minutes. The biggest advantage is its build time - a staggering average build time of under 2.5 hours with a full platform of crown and bridge models. All this with 35 micron resolution in Z. This means the lab is able to complete several builds in an 8 hour shift, allowing for fast turnaround of highly detailed accurate models. Unattended production means the machine can work while you are away. It will even turn itself off after completing a build.

| Material Properties* | |
|--|----------------|
| Description | Value |
| Tensile Strength | 56 MPa |
| Elongation at Break | 3.5% |
| Flexural Strength | 115 MPa |
| Flexural Modulus | 3350 MPa |
| HDT (Heat Deflection Temperature) No heat treatment necessary | 140° C (284°F) |

*All data provided is preliminary data and must be verified by the individual user.

| Recommended Machines |
|--|
| Perfactory® Micro EDU, Perfactory® Micro Ortho, Perfactory® Micro XL |

| Applications |
|---------------------|
| Dental, Orthodontic |



EnvisionTEC GmbH

Brüsseler Straße 51 • D-45968
Gladbeck • Germany
Phone +49 2043 9875-0
Fax +49 2043 9875-99

EnvisionTEC, Inc.

15162 S. Commerce Dr.
Dearborn, MI 48120 • USA
Phone +1-313-436-4300
Fax +1-313-436-4303

www.envisiontec.com

info@envisiontec.com