



GE
Lighting



Reflector

OT 42W HALO R63/E27 240V GE TRBX 1/6
MIC

95116

Product information

GE's HaloReflector range is a direct replacement for regular incandescent lamps offering a crisp white light. These bulbs are the environmentally friendly solution for those who prefer the features and light quality associated with incandescent bulbs.

- Last twice as long and consume up to 30% less electricity than corresponding incandescent lamps.
- Provide instant-on, full light output at start-up and lumens are maintained throughout the life of the product.
- Unlike some compact fluorescent products, these lamps are 100% retrofit with the incandescent lamps they replace.
- Can be used with dimming switches.
- Environmentally friendly with no lead or mercury.
- Up to 2,000 hours life
- Excellent colour rendering, light close to natural (100% CRI)

- More than 90% lumen maintenance over life
-

Product data

Cap/Base	E27
Bulb Shape	Reflector
Bulb Diameter [mm]	63
Bulb maximum overall diameter [mm]	105
Maximum Overall Length [mm]	105
Net weight per piece [g]	38
Gross weight per piece [g]	56
Brand	General Electric (GE)

Performance data

Nominal correlated colour temperature (CCT) [K]	2600
Rated beam angle [°]	30
Rated peak intensity in [Cd]	530
Rated Lumens [lm]	280
Energy efficiency class (EEC)	D
Rated Life [h]	2000
Nominal power [W]	42
Nominal lamp voltage [V]	240

Electrical data

Rated power [W]	42.2
Weighted energy consumption [kWh/1000h]	43.51
Run-up time (sec)	Instant startup
Starting time [sec]	Instant startup
Number of switching cycles	8000
Dimming Capability	Yes

Logistic data

DUN Code	10043168951163
EAN Code	0043168765411
Pack Quantity	6
Layer quantity	186 EUR, 234 UK
Layer quantity EUR	186
Layer quantity UK	234
Pallet quantity EUR (PC)	1674
Pallet quantity UK (PC)	2106
Outer case size	206 x 141 x 117 (mm)
Product status	Available

Application areas



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Halogen Lamps Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)