







Pulse Transforme Comparison chart

September 29, 2017
Magnetics B. Group.
TDK Corporation

	Current product		Proposed product		Change point																														
Product name	Pulse Transforme ALT3232M-151-T001 		Pulse Transforme ALT3232M-151-T001 		No Change																														
Shapes and dimension	   Unit : mm Appearance		   Unit : mm Marking $\varnothing 0.5$ Appearance		Change																														
Product spec.	Operating Temp.	-40deg.C to 85deg.C	Operating Temp.	-40deg.C to 85deg.C	No Change																														
	Inductance(DC Bias 8mA)100kHz	150 μ H Min	Inductance	150 μ H Min																															
	Insertion Loss 0.1~100MHz	2.5dB Max	Insertion Loss 0.1~100MHz	2.5dB Max																															
	Capacitance 100KHz	25pF Max	Capacitance 100KHz	25pF Max																															
Machine	—		—		No Change																														
Material	 <table><thead><tr><th>No.</th><th>ITEM</th><th>MATERIAL</th></tr></thead><tbody><tr><td>1</td><td>SP Core</td><td>Ni-Zn</td></tr><tr><td>2</td><td>DR Core</td><td>Ni-Zn</td></tr><tr><td>3</td><td>Wire</td><td>Polyurethane Wire</td></tr><tr><td>4</td><td>Metal Terminal</td><td>Copper Alloy + Plating: Ni+Sn</td></tr></tbody></table>		No.	ITEM	MATERIAL	1	SP Core	Ni-Zn	2	DR Core	Ni-Zn	3	Wire	Polyurethane Wire	4	Metal Terminal	Copper Alloy + Plating: Ni+Sn	 <table><thead><tr><th>No.</th><th>ITEM</th><th>MATERIAL</th></tr></thead><tbody><tr><td>1</td><td>SP Core</td><td>Ni-Zn</td></tr><tr><td>2</td><td>DR Core</td><td>Ni-Zn</td></tr><tr><td>3</td><td>Wire</td><td>Polyurethane Wire</td></tr><tr><td>4</td><td>Metal Terminal</td><td>Copper Alloy + Plating: Ni+Sn</td></tr></tbody></table>		No.	ITEM	MATERIAL	1	SP Core	Ni-Zn	2	DR Core	Ni-Zn	3	Wire	Polyurethane Wire	4	Metal Terminal	Copper Alloy + Plating: Ni+Sn	No Change
No.	ITEM	MATERIAL																																	
1	SP Core	Ni-Zn																																	
2	DR Core	Ni-Zn																																	
3	Wire	Polyurethane Wire																																	
4	Metal Terminal	Copper Alloy + Plating: Ni+Sn																																	
No.	ITEM	MATERIAL																																	
1	SP Core	Ni-Zn																																	
2	DR Core	Ni-Zn																																	
3	Wire	Polyurethane Wire																																	
4	Metal Terminal	Copper Alloy + Plating: Ni+Sn																																	
Method	—		—		No Change																														