

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




24 V DC Nanoline base unit. Equipped with 8 digital inputs, 2 analog (0-10 V) inputs and 4 relay output channels. Additional I/O channels can be added using a maximum of three I/O extension modules. Optional communication modules provide network or serial connectivity. Optional Operator Panel provides user interface. Programming is via nanoNavigator.

Why buy this product

- An operator panel can be integrated in the basic unit or installed remotely on a panel as an option
- Intuitive programming language with options for flowcharts and ladder diagrams
- Basic unit has integrated digital inputs, relay outputs, and analog inputs, including high-speed counters



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 576611
Weight per Piece (excluding packing)	331.5 g
Custom tariff number	85371099
Country of origin	India

Technical data

Dimensions

Width	80.5 mm
Height	103.5 mm
Depth	60 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	90 %

Interfaces

Interface	Operator Panel
Connection method	RJ45 / Combicon
Interface	V.24 (RS-232)

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Technical data

Interfaces

Connection method	Slot 1
Interface	USB
Connection method	Slot 1

Supply

Power supply connection	Screw connection
Supply voltage	24 V DC (Power available to the I/O and Communications modules)
Supply voltage range	19.2 V DC ... 30 V DC
Max. current consumption	250 mA
Typical current consumption	150 mA

Software interfaces

Programming tool	nanoNavigator 3 or above
------------------	--------------------------

Digital inputs

Input name	Digital inputs
Description of the input	EN 61131-2 type 1 NPN/PNP
Connection method	Screw connection
Number of inputs	8
Typical response time	20 ms (on) 70 µs (off)
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input current at U _{IN}	5 mA DC (On)

Digital outputs

Output name	Relay output
Output description	Relay output
Connection method	Screw connection
Number of outputs	4
Protective circuit	External protection required
Nominal output voltage	24 V DC
Maximum output current per channel	5 A
Maximum output current per module / terminal block	20 A
Maximum output current per module	5 A
Nominal load, ohmic	600 W (@ 24 ohms)

Analog inputs

Number of inputs	2
Connection method	Screw connection
Resolution A/D	12 bit (monotonic)
Limit frequency (3 dB)	1 Hz (3 dB)
Type of protection	Transient voltage suppression

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Technical data

Analog inputs

Measuring principle	Successive approximation
Voltage input signal	0 V DC ... 10 V DC
Input resistance of voltage input	20 k Ω
Precision	2 % (full-scale)
Input filter	Digital

Counter inputs

Number of inputs	2
Input frequency	6 kHz

General

Mounting type	DIN rail
---------------	----------

Classifications

eCl@ss

eCl@ss 4.0	27240101
eCl@ss 4.1	27240101
eCl@ss 5.0	27242216
eCl@ss 5.1	27242216
eCl@ss 6.0	27242216
eCl@ss 7.0	27242216
eCl@ss 8.0	27242216

ETIM

ETIM 3.0	EC001417
ETIM 4.0	EC001417
ETIM 5.0	EC001417

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Listed

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Approvals

Ex Approvals

Approvals submitted

Approval details

UL Listed 

Accessories

Accessories

Communication module

nanoLC module - NLC-MOD-RS232 - 2701179



RS-232 connection for data transfer or software configuration

Option module - NLC-MOD-RS485 - 2701182



RS-485 connection for data transfer or software configuration

nanoLC module - NLC-MOD-USB - 2701195



Serial connection to PC's USB port for data transfer or software configuration

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Accessories

Communication module - NLC-COM-ENET-MB1 - 2701124



Ethernet communication module. Allows the Nanoline controller to be connected to an Ethernet, operating as a Modbus TCP Server.

Communication module - NLC-COM-GSM - 2701344



GSM communication module. Allows SMS messaging to and from the Nanoline controller when connected to the GSM network.

Cover

Covering hood - NLC-MOD-CAP-PXC - 2701292



Replacement cover for slot 2 in base unit.

Covering hood - NLC-MOD-CAP - 2701289



Replacement cover for slot 1 in base unit.

Extension module

I/O extension module - NLC-IO-06I-04QTP-01A - 2701072



I/O extension module for use with Nanoline base unit. Equipped with 6 digital input and 4 PNP digital output channels. A maximum of three I/O extension modules can be attached to a base unit.

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Accessories

I/O extension module - NLC-IO-06I-04QTN-01A - 2701085



I/O extension module for use with Nanoline base unit. Equipped with 6 digital input and 4 NPN digital output channels. A maximum of three I/O extension modules can be attached to a base unit.

I/O extension module - NLC-IO-03I-04QRD-05A - 2701328



I/O extension module for use with Nanoline 24 V DC base unit. Equipped with 3 digital input and 4, 5 A relay output channels. A maximum of three I/O extension modules can be attached to a base unit.

I/O extension module - NLC-IO-4AI - 2701098



I/O extension module for use with Nanoline base unit. Equipped with 4 analog input channels. A maximum of three I/O extension modules can be attached to a base unit.

I/O extension module - NLC-IO-2AI-2AO-01 - 2701040



I/O extension module for use with Nanoline base unit. Equipped with 2 analog input (0...10 V DC, -10...+10 V DC, 0/4...20 mA) and 2 analog output (0...10 V DC, 0/4...20 mA) channels. A maximum of three I/O extension modules can be attached to a base unit.

Mounting material

Mounting kit - NLC-OP1-MKT - 2701140



Mounting kit

Operator interface

base unit - NLC-055-024D-08I-04QRD-05A - 2700464

Accessories

Operator terminal - NLC-OP1-LCD-032-4X20 - 2701137



User interface for Nanoline controllers. Mounts directly on the base unit. Can be mounted remotely using the mounting kit.

Programming cable

Conductor - NLC-PC/SERIAL-CBL 1M - 2701234



Cable, serial, 9-pos. D-SUB to RJ11/12


Conductor - NLC-PC/USB-CBL 2M - 2701247



Cable, serial

Drawings

Connection diagram



Dimensioned drawing

